

FS33 IR series

Solid state LED DLP® projector



Barco's FS33 IR projector is the world's most realistic night vision simulation projector. With its 2nd generation LED illumination system, you get 50% more light than any other LED-illuminated projector. Even in pitch black conditions, you are still capable of making out various light points (such as head lights, street lights, or runway lights) for a true-to-life simulation, thanks to its 0 – 100% visual RGB adjustments. Its optics are purpose designed, specifically developed for IR transmission. Adjustable SRP™ Smear Reduction Processing guarantee a smear and jitter free image. A LED-lit projector, the FS33 IR will improve the operation up-time, and drastically reduce maintenance and operating costs and required technical resources.

Control your cost of ownership with ReaLED™

With no lamps, our 2nd generation patented ReaLED™ IR and RGB LED illumination engine provides up to 100,000 hours of life time expectancy. There are no re-calibration requirements, no color degradation and no foreseeable maintenance. With the FS33 IR you have a perfect projector for all visible video and NVG IR stimulation requirements. With its unique 4-LED engine, it can accurately project day and night imagery simultaneously.

Unlimited installation flexibility

Not restricted by lamp technology, the FS33 IR can be placed in any orientation angle thinkable. With its comprehensive, and very high quality projection lens options and industry standard mounting, the FS33 IR further greatly simplifies installations and keeps infrastructure costs down. There is only one cabinet, complete with optics, I/O, processing, and control. The complete system's weight is limited to 16 kg (35 lbs.), complete with the lens mounted. The result is a projector

Not restricted by lamp technology, the FS33 IR can be placed in any orientation angle thinkable. With its comprehensive, and very high quality projection lens options and industry standard mounting, the FS33 IR further greatly simplifies installations and keeps infrastructure costs down. There is only one cabinet, complete with optics, I/O, processing, and control. The complete system's weight is limited to 16 kg (35 lbs.), complete with the lens mounted. The result is a projector that is rugged enough to be integrated onto motion platforms or in simple truss systems, in any orientation angle.

The uniqueness of FS33 IR

- IR LED for NVG stimulation
- 2nd Generation solid state LED
- 1000 lumen brightness
- 1920 x 1200 or 1080p native resolution
- 810 nm IR wavelength (850 nm optional)
- 0-100% adjustable visible RGB
- Full spectrum display (RGB + IR)
- Adjustable SRP™ smear reduction processing
- Up to 100.000 hours service life
- Designed for 24/7 operation
- Designed for multi-channel systems
- Unique colour matching capabilities with RealColor™
- Unrestricted installation flexibility
- Wide range of Ultra HQ projection lenses

Product specificaties**FS33 IR SERIES****General specifications**

Concept	RealLED™ IR technology, all-glass optical design with lens shift
Resolutie	1080p (1920 x 1080) WUXGA (1920 x 1200)
Helderheid	Up to 1000 lumens (Infinitely adjustable)
Contrast	Up to 4000 : 1 (16:9 (1080p) 16:10 (WUXGA))
Technologie	2nd Generation Solid State LED based single chip DLP® projector
Beeldverhouding	16:9 (1080p) 16:10 (WUXGA)
Beeldschermkleuren	40-bit RGB + IR
Latentie	~22 ms on graphics port
Grafische indelingen computer	1920x1200
Horizontale scanfrequenties	10 -150 kHz (resolution dependant)
Verticale scanfrequenties	50 -110 kHz (resolution dependant)
Videoformaten	HDTV (1080p, 1080i, 720p)
Lenswerking	Motorized zoom, Focus, Shift, Iris and Mechanical shutter
Beeldbreedte	0.7 -5 m
Infraroodgolflengte	810 nm
Lichtbron	LED
Levensduur lamp	Up to 100.000 hours
Computeringangen	1 x HDMI 1.3a 1 x DVI-D 1 x 5-BNC 1 x VGA 1 x XPort1 1 x XPort2
Video-ingang	1 x HDMI 1.3a 1 x YPbPr 1 x S-video 1 x Composite
Controlemogelijkheden	1 x RJ-45 TCP/IP 2 x 9-pin D-SUB RS232 1 x USB 2 x 12V programmable trigger (3.5mm mini jack) 1 x Wired Remote 3.5mm mini jack
Afmetingen	510 x 223 x 376 mm (WxHxD)
Gewicht	12.6 kg
Verzendingsafmetingen	520 x 370 x 780 mm (WxHxD)
Verzendgewicht af fabriek	20 kg
Voedingsvereisten	Certified rating: 8.4A, ~100-240V, 50-60Hz Typical consumption: Max 325W@100V, ~2.7A, 50Hz; ~1.2A, 240V, 50Hz
Bedrijfstemperatuur	10 -40 °C
Opslagtemperatuur	-20 -60 °C
Hoogte	Up to 3000 m
Vochtigheid in bedrijf	20-80%
Vochtigheid bij opslag	10-90 %
Kleur	Black metallic
Garantie	Limited 3 years parts and labour Up to 5 years total extended warranty available Conditions apply
Altijd beschikbare documentatie	This projector is designed and warranted for heavy duty 24/7 operation. Specific measures and design considerations have been made in order for it to comply with stringent requirements in challenging applications.
MTBF	56,834 hours
BTU/uur	

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.