

RLM R6+ Performer

<P>SXGA+, 6,000 lumens three-chip DLP projector</P>



Spécifications techniques**RLM R6+ PERFORMER****Spécifications générales**

Luminosité	6500 Center lumen 6000 ANSI Lumen
Résolution	1400 x 1050 (native)
Uniformité de la luminosité	> 90% for the total screen
Taux de contraste	1600:1 (full field)
Affichage	3 Chip DLP SXGA+ (resolution of 1400 x 1050 pixels (aspect ratio 4:3)).
Convergence	Max allowed convergence drift is 0.5 pixel. This is checked on vertical and horizontal midlines only. Corners are not applicable for convergence error. This is measure with TLD 1.2 lens on axis.
Caractéristiques	■ Autolmage ■ Advanced picture-in-picture ■ Seamless switching with effects ■ Standard light shutter ■ Advanced digital zoom ■ Rigging point ■ Carrying handle ■ Frame ■ P7 color processing
Image dans l'image	Up to 4 sources simultaneously (2 data, 1 video and 1 SDI)
Entrées	Fixed inputs ■ 1x Configurable 5-Wire (BNC) ■ 1x Composite Video (BNC) ■ 1x S-Video (4-pin mini-DIN) ■ 1x analogue RGB (D15 connector) ■ 1x SDI/HDSDI (+ loop through) ■ 1x DVI (Digital Visual Interface)
Sorties	HDSDI/ SDI loop out
Communication	■ 1x RS-232C IN (D-9 connector) ■ 1x RS-232C OUT (D-9 connector) ■ 1x RS-232C IN (XLR connector) ■ mini-jack for wired remote control
Compatibilité	■ All current video sources (PAL, SECAM, NTSC) in Composite, S-VHS, Component or RGB formats ■ All currently proposed HDTV, extended and improved television standards (1080i, 720p) ■ All computer graphics formats from VGA, SVGA, XGA, SXGA,full HD to UXGA ■ Most Macintosh computers ■ Electronic workstations with a resolution up to 1600 x 1200 pixels at 75 Hz ■ Most computer sources with a pixel clock up to 200 MHz ■ DVI sources up to SXGA+
Compatibilité avec les sources en entrée	1600 x 1200 (max. input)
Taille d'écran	From 1-7m / 3-23ft.recomended
Fréquences de balayage	Pixel clock >162Mhz (UXGA 60hz)
Connexion réseau	Optional (10 base-T)
Température ambiante	Max 40°C (104°F)
Lampe	2 x 250 W mercury Lamp warranty: 1000 hrs

Spécifications techniques

RLM R6+ PERFORMER

Lentilles	Lens	Order Nr
	TLD (HB) 0.8	R9842040
	TLD (HB) 1.6 - 2.0	R9842060
	TLD (HB) 2.0 - 2.8	R9842080
	TLD (HB) 2.8 - 5.0	R9842100
	TLD (HB) 5.0 - 8.0	R9842120
Décalage de la lentille	Vertical: -10% to +110% Horizontal: -50% to +50% (small differences occur per lens type)	
Codeurs de lentilles	On zoom and focus (with TLD lenses)	
ScenergiX	Standard horizontal and vertical electronic edge blending	
Cœur de processeur DLP™ scellé	Standard	
Filtres à poussières	Metal filters	
Niveau sonore	42 dB(A) (at 40°C)	
Tension secteur	92-240 V / 50 -60 Hz	
Consommation électrique	700 W	
Dissipation d'énergie	Max 2217 BTU/h	
Alimentation CA	90V -255V (50 Hz -60Hz)	
Poids	Projector: 25 kg (56 lbs) Frame: 5 kg (11 lbs)	
Dimensions	W x L x H 705 x 707,8 x 316,5 mm (27.8 x 27.9 x 12.5 inch)	
Dimensions à l'expédition	Width: 56 cm Height: 100 cm Depth: 100 cm Floor Space: 1 m ² Volume: 0,56 m ³ Gross Weight: 65 kg	
Réglementations en matière de sécurité	Compliant with UL1950 and EN60950	
Interférence électromagnétique	Complies with FCC rules & regulations, part 15 Class A and CE EN55022 Class A	
Référence	Projector body (without lens): R9010270 Spare dual lamp: R9852940	

Crée le : 09 Jul 2024

© 2024 Barco nv. Tous droits réservés. La reproduction partielle ou intégrale sans autorisation écrite préalable est interdite. Les noms de marques ou de produits sont des marques commerciales, des marques déposées ou des appellations commerciales appartenant à leurs détenteurs respectifs. Pour des raisons d'innovation continue, les informations et les caractéristiques techniques sont susceptibles d'être modifiées sans préavis. Veuillez consulter www.barco.com pour les dernières spécifications.

