

ClickShare Hub Pro

Premium modular video conferencing room system for enhanced hybrid meetings

- **Wireless presentation: 4K content sharing with 2 next-gen ClickShare Buttons with USB-C DisplayPort™**
- **Dual display support**
- **100% secure, encrypted, cloud-managed**
- **Sustainable product with Barco Eco label A+**

ClickShare Hub Pro is a premium modular, wireless video conferencing system for enhanced hybrid meetings. Featuring two next-gen ClickShare Buttons (with Wi-Fi 6E and USB-C DisplayPort™), it ensures meeting participants enjoy secure, 4K wireless content sharing. With dual display support, it guarantees highly visual and engaging meetings.

For IT managers and integrators, ClickShare Hub Pro offers a customizable solution for all room types, enterprise-grade security and compliance.

Expected to be available end of 2025.

Product specifications

CLICKSHARE HUB PRO

General specifications

Operating system	Windows 10 or higher macOS 14 (Sonoma) and 15 (Sequoia)
System requirements	For a smooth experience with Microsoft Teams or Zoom Minimum: Intel i3 dual-core processor or AMD Ryzen 7 /8GB RAM / OS: Windows 10 latest build or Mac OS Mojave latest build Recommended: Intel i5 4-core processor or AMD Ryzen 9 / 8GB RAM / OS: Windows 11 latest build or Mac OS latest build
Video outputs	HDMI-1: UW5K WUHD (5120*2160) @30Hz HDMI 2.0 HDMI-2: 4K UHD (3840*2160) @30Hz HDMI 2.0 eDP (Touch Console): HD (1280*800) @60Hz DP 1.4
Video inputs	4K UHD (3840*2160) @30Hz HDMI 2.0
Audio output	USB, HDMI, BT
ClickShare Buttons	2
Noise Level	Maximum 25 dBA @ 30°C
Wireless transmission protocol	IEEE 802.11 a/b/g/n/ac/ax/be and IEEE 802.15.1 BT 5.3
Reach	Max. 30m (100ft) between ClickShare Button and ClickShare Base Unit Frequency band 2.4GHz, 5 GHz and 6 GHz (DFS)
Frequency band	2.4GHz, 5GHz and 6GHz DBS/HBS (DFS channels supported in select number of countries)
Connections	Back: 1x Ethernet LAN 1Gbit 1x USB-C Power delivery 3.1 EPR sink 2x HDMI output 2x USB-C 2.0/3.0 1x USB-A 2.0/3.0 1x USB-C 2.0/3.0 Device + USB-C DisplayPort™ output 1x USB-C 2.0 + USB-C DisplayPort™ output Front: 1x USB-C 2.0/3.0
Temperature range	Operating: 0°C + 40°C (+32°F to +104°F) Max 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	Kensington lock
Certifications	FCC/CE
Network connection	LAN
Management and reporting	Yes
Warranty	3 years standard
*	At a later stage

ClickShare Base Unit dimensions

Dimensions (HxWxD)	37 * 180 * 180 (mm)
Power consumption	Operational: 160W (max) Standby:
Power supply	External USB-C charger 100W (PD3.0 SPR), 180W (PD3.1 EPR)
Weight	720gr

Last updated: 04 Jun 2025

© 2025 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.