

DLite 7

The BARCO DLite 7 is the high resolution, indoor & outdoor LED display for various applications.



Product specificaties

DLITE 7

General specifications	
Visuele resolutie	7,0 mm
Fysieke resolutie	14,0 mm
Helderheid	6500 NIT 5000 NIT (calibrated @ 6500°K)
Led-configuratie	2R, 2G, 1B
Pixeldichtheid	20.407/m² (1.898/ft²) 4.096/tile
Hor. kijkhoek	120° (min.50% brightness)
Vert. kijkhoek	60° (min.50% brightness)
Levensduur	50 000 h (full white -half brightness)
Energieverbruik	maximum: 250 W / Tile average: 62 W / Tile
Gewicht / tegel	14 Kg / 30,8 lbs (excluding structure)
Verwerking	color : +10 bit
Kleuren	1,07 billion
Vernieuwingssnelheid	400 Hz minimum (PAL / NTSC)
Temperatuurbereik	operating : -20°C -40°C (-4 -104°F) storage : -20°C -60°C (-4 -140°F)
Vochtigheid	operating: 10 -99% storage: 10 -99%
D320-invoercompatibiliteit	S-Video -Composite -YUV -RGB -SDI -HDSDI -Data DVI up to UXGA
Certificeringen	UL -CE -TUV -FCC Class A
Paneelafmetingen	width: 448mm (17.6") height: 448mm (17.6") depth: 195mm (7.7")

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

