

ClickShare X-Display 65"

ClickShare X-Display, designed around your laptop (BYOM), integrates advanced audio, video, and display capabilities to deliver a seamless hybrid meeting experience.



- **16 Microphone array with a 12-meters range for precise audio capture**
- **AI-driven noise reduction, AI sound masking, and echo cancellation**
- **High-quality, immersive stereo sound**
- **4K 50-megapixel ultra-clear camera**
- **400nits high-brightness anti-glare display for clear visibility**
- **Expandable with a variety of third-party peripherals**

ClickShare X-Display is a cutting-edge solution that integrates audio, video, display, and collaboration features, designed to elevate hybrid working environments. Featuring a 16 Microphone array and a 4K 50-megapixel high-definition camera, it guarantees a superior audio-visual experience. Fully compatible with major cloud platforms and devices, it ensures a seamless, efficient, and stable meeting experience with minimal setup required.

Product specifications**CLICKSHARE X-DISPLAY 65"**

Display	
Size	65-inch
Type	LCD
Resolution	4K UHD (3840*2160)
Contrast ratio	4000:1
Brightness	400 cd/m2 [typical]
Color gamut	94% P3 [typical]
Color accuracy	ΔE
Backlight type	D-LED
Panel	<ul style="list-style-type: none">• Anti-glare• Anti-ambient light interference, Clearer display
Refresh Rate	60Hz
Camera	
Pixels	50 MP
Sensor source	SONY
Resolution	4K, 1080p, 720p at 30fps
FOV	99°
Pixel size	1.0 μm
ZOOM	5x digital zoom
WDR	Yes
Distortion correction	Yes
Lens cap	Manual slide cover
AI function	
Group Framing	Yes
Composition mode	Yes [up to 8 people]
Speaker framing	Yes
Intelligent tracking	Yes [Speaker framing with panoramic view]
AI soundscreen	Yes [30°/60°/90°/180° -4 level available]
Speaker AI adaptive	Yes [According to the different acoustic environment of the meeting space, the sound effect of the Speaker is automatically adjusted to fit the current meeting space]
Microphone	
Quantity	16 beamforming MEMS microphones
Hardware accelerated audio processing	Yes
Pickup distance	up to 12 meters
Sound pickup angle	180°
Echo cancellation	Yes
Noise suppression	Yes [More than 300 types of noise can be suppressed]
Automatic gain control	Yes
Dereverberation	Yes
Speaker	
Channel	2.1 Channel stereo
Quantity	5 Speaker units (separate bass speakers)
Frequency Domain	60 Hz to 20KHz
Output Power	2x15W+20W
Position	Top
General specifications	
Dimensions (W*D*H)	1465.1*77.7*912mm
Weight	35.185 kg [gross weight] 30.19 kg [net weight]
Expansion capability	
Support extend Microphone (Cascade mode)	Yes [up to 4 ClickShare Wireless Speakerphone]
Third-party USB peripherals	Yes
OPS	CX-M [optional]
Connections	
HDMI IN	2 [HDMI 2.0]
HDMI OUT	1 [1080p / 2160p]
USB-C (front)	1 [front]
USB-C (board)	1 [board]
USB-B (2.0)	1
USB-A (3.0)	2
USB-A (2.0)	1 [only for X-Display upgrading]
RJ45 (MIC IN)	1 [connect to ClickShare Wireless Speakerphone]
Audio Out	1 [SPDIF]

Product specifications	CLICKSHARE X-DISPLAY 65"
RS232	1DB9, 1
RJ45 (1Gbps)	2Ethernet
Accessories	
Cable	Power cord x 1
Remote control	1
Wall-mounted bracket	Yes
Floor stand	Optional
Storage Box	Yes
Type-C Cable	Yes
Power	
Power Supply	AC100 to 240V, 50/60Hz
Power Cord	China, length 3Meters
Max Operating Power Consumption	< 180W
Max Standby Power Consumption	< 0.5W
Environment	
Operation Temperature	0°C~40°C
Operation Humidity	10% ~ 90% RH
Storage Humidity	10% ~ 90% RH
Storage Temperature	-20°C~60°C
Altitude	0 5000metres
Compliance	
EMC/Safety	CCC/CE
Energy	China Energy Label2
RoHS	China RoHS

Last updated: 16 Apr 2025

© 2025 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.