

PDS-4K

Small venue presentation switcher with 4K capabilities



- premium 4K visuals
- simple setup and easy to operate
- compatibility for smooth integration

The PDS series is designed to meet today's requirements for a high-quality, easy-to-use and fast seamless switcher with more digital inputs at an affordable price. It is the perfect fit for mid-sized live events, breakout sessions, seminar rooms and boardrooms.

4K for you

The PDS-4K enables single screen, dual screen and quad screen switching with high-quality 4K processing, and it can also support Dante® audio with the addition of an optional interface card. It includes six HDMI 2.0 inputs and four fully seamless mixing program outputs at up to 4K resolution. Benefit from the ultra-low latency processing (≦ 2 frames delay @60Hz), smooth video display and seamless transitions between inputs to maximize audience engagement. Additionally, you can increase interactivity by showing up to two live inputs simultaneously with the available PiP layers. And the Event Master Athena™ scaling technology guarantees superior signal clarity and minimum scaling artifacts.

PDS: pretty darn simple

The PDS-4K switcher guarantees unsurpassed performances and outstanding visual experience while also being exceptionally easy to operate. With just one simple press on the buttons of the intuitive front panel interface, you can switch easily between the input sources and preconfigured layouts. What's more, the PDS-4K is compatible with all the familiar Barco visualization solutions and presentation devices (e.g. ClickShare) without compromising on video quality. The PDS-4K can be controlled with Event Master Toolset, and thanks to the API it can also be combined with other third-party control panels.

The PDS-4K is built for applications requiring the highest availability and uptime. The switcher also proves to be a smart investment well into the future with option cards to ensure expandability and future-proof upgradability.

Product specificaties**PDS-4K**

General specifications	
Live-effectencanvas	2x outputs up to 4K60 or 4x outputs up to 4K30 each with single mixing PiP or two non-mixing PiPs on a still background
Video-ingangen	6x HDMI 2.0 connectors
Video-uitgangen	4x HDMI 2.0 connectors
Programma-uitvoer	Two UHD @60 PGM or Four UHD @30 / FHD @60 PGM
Mixers	1 mixer per PGM output
Keying/mixing	Luma and Chroma on non-mixing PiPs
Geheugenruimte voor foto's	Eight stills, up to 4K each
Multiviewer	1x UHD@60 output with user definable layouts consisting of inputs plus PVW and PGM for each screen
Uitbreidbaarheid	Option card slot for other video connector types and/or Dante® audio
HDCP	HDCP 1.x and 2.2
Controle	<ul style="list-style-type: none">■ front panel mappable buttons■ Event Master screen management software for PC or MAC■ Event Master controllers■ WebUI■ Ethernet RJ-45, 1000/100/10 Mbps autosense
Geluidsniveau	37 dB in a room temperature environment (23°C/73°F)
Garantie	3 years parts and labor
Afmetingen (H x B x D)	6.62 cm (2.605 in) x 48.41 cm (19.06 in) x 40,9 cm (16.1 in)
Gewicht	6.21 kg (13.7 lbs)
Omgevingstemperatuur	0-40° C (32-104 F)
Vermogen	Input power: 100-240 VAC 50/60Hz 151W
Omgevingsvochtigheid	0-95% non-condensing (non-operating) 0-85% non-condensing (operational)
Opmerkingen	Option Card slot to support additional video input connectors, embedded audio processing and Dante® Audio

Laatst bijgewerkt: 03 Nov 2023

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.