

SLM G5 Performer

A Compact and Smokeproof Projector for Rental & Staging Applications



- Enhanced low-light video performance is the result of its newly designed pixel map processor.
- Integrated Constant Light Output (CLO), which can be linked with other G5 projectors for use in multi-screen applications.
- True seamless switching includes transition effects such as cross-fade, wipe, etc.
- Carrying handle with integrated rigging system.
- The unique "click-and-play" lenses make it possible to exchange lenses in seconds.
- Direct stacking and interlocking design enable an easy and stable setup
- Sealed optics significantly reduce optical system maintenance, which allows the G5 to be used at events where smoke generators are involved.
- Modular structure provides greater accessibility to serviceable parts.
- The optical system's compact and lightweight lens range is designed for the continuing evolution of the DLP technology.

Specifiche tecniche**SLM G5 PERFORMER**

Specifiche generali	
Emissione luminosa	5.000 ANSI lumens
Risoluzione	1024 x 786 (native) 1600 x 1200 (max)
Risoluzione	1024 x 786 (native) 1600 x 1200 (max)
Digital MicroMirror Device™	3 high resolution XGA DMD's
Uniformità della luminosità	> 90% for the total screen area
Contrasto	500:1 (full white/full black) 500:1 (full white/full black)
Lampada	Lifetime (max): 1500 Hrs Lifetime (typ): 1000 Hrs Lamp Power: 1,2 kW
Livello di rumore (a 20° C)	< 43
Livello di rumore (a 40° C)	< 50
Tensione di alimentazione	110/230 V
Consumo energetico	1.600 W
Temperatura ambiente	40°C (104F) max
Dimensioni	875 mm x 585 mm x 429 mm 34,5" x 23" x 16,9"
Peso (compresi elementi di assemblaggio)	56 kg / 124 lbs
Ottiche	BARCO's "click-and-play!" TLD lenses provide the highest quality picture. Available both in fixed and zoom versions.
Spostamento obiettivo	Motorized V shift: up to 118 % Motorized H shift: up to 65 %
Elemento centrale DLP™ sigillato	Yes
Commutazione continua	Standard
ScenergiX	Standard
Ingressi fissi	<ul style="list-style-type: none">• 2 Multifunctional 5-cable inputs for the connection of RGB analogue signals with standard sync (BNC connectors) or tri-level sync, sync on green or separate sync, Standard Video signals, S-VHS signals• 2 Multistandard DVI• SDI input (Serial Digital Input)
Ingressi opzionali	One free digital input slot for optional input modules: <ul style="list-style-type: none">• SDI• HD -SDI
Comando da remoto	<ul style="list-style-type: none">• RS232 or RS422 loop-through input (D9-connector) for PC based projector control• Communication input (D9-connector) for peripherals• 3 pin male XLR connector for wired remote (standard remote)• 3 pin female XLR connector for bi-directional communication (rugged remote)

Generato il: 15 Mar 2023

Le informazioni e i dati forniti riguardano l'apparecchiatura descritta. Tuttavia ogni singolo articolo è soggetto a modifiche senza preavviso.
 L'ultima versione di questo opuscolo è disponibile all'indirizzo www.barco.com.