


# Ushio 7000W DXL-70BA

This lamp is not compatible with all units. Check the serial number of your projector.



Requires training and tools from kit R9854425.

First check the serial number of your projector with Barco's service team.

**Product specifications****USHIO 7000W DXL-70BA**

General specifications	
Supplier	Ushio
Supplier order numbers	DXL70BA-Z1
Warranty hours	n.a.

Last updated: 15 Mar 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.