

Balder

A divine force, bringing beauty and life to the most refined home cinema and media rooms.



- Theater & Media Room Series
- 4K UHD Resolution (3,840 x 2,160)
- Laser Phosphor
- Up to 7,000 ANSI Lumens

Manufactured to perfection in Belgium, Balder is built from the highest quality materials including aluminium, magnesium and glass. Balder not only shares the same Ultra HD and HDR compatible Pulse electronics as Loki, the optical design and single laser engine are also taken from the Loki platform.

Professional grade optics

By basing Balder's optical engine on its bigger brother Loki's architecture, which features custom designed aspherical glass elements and enhanced low dispersion glass lenses, image quality is in a class of its own.

Topping that, Balder's chassis and core are built from aluminium and magnesium, which offer exceptional robustness, resulting in the best picture quality ever shown at this level.

State of the art electronics

Our "Pulse" electronics are built on a superior FPGA platform, featuring a dual core processor on the industry's only 20 nm SoC, with 96 transceiver lanes delivering 3.3 Tbps of serial bandwidth.

Thanks to our unique single step processing technology (SSPTM), Pulse electronics are designed to process 4K UHD, HDMI 2.0a, HDCP 2.2 and HDR10 signals with extremely low latency. This provides exceptional gaming and movie viewing experiences.

Laser light source

Outstanding image quality requires an exceptional light source, which is why Balder uses our brand-new laser engine which delivers up to 7,000 ANSI lumens output.

Alongside significantly improved image uniformity, lasers last longer than traditional projector lamps, offer great image quality consistency over their lifetime, are less fragile and offer near instant on/off performance.

Liquid cooling

Balder has departed from a pure fan based cooling system, opting instead for a liquid cooling PID regulation system. This combined with our simulation grade warp engine allows Balder to operate at any angle (free rotation), offering new possibilities when it comes to architectural integration.

Spécifications techniques

BALDER

Spécifications générales	
Type de projecteur	Single chip DLP
Technologie	0.9" DMD™
Résolution	3,840 x 2,160 (4K UHD)
Rapport d'aspect	1.78:1 (16:9)
Source lumineuse	Laser phosphor
Durée de vie de la source lumineuse	20,000 - 60,000 hours Laser intensity dependent
Luminosité	DCI (P3) Color Wheel: Up to 4,000 ANSI lumens T Color Wheel: Up to 5,000 ANSI lumens M Color Wheel: Up to 7,000 ANSI lumens
CLO (constant light output/sortie lumineuse constante)	Yes
Taux de contraste	1,800:1 Sequential 450:1 ANSI
Uniformité de la luminosité	>90%
Gamme de lentilles	(R9802232) -EN68 (0.30:1) -Periscope Lens (requires vertical installation) (R9801832) -FLDX UST (0.41:1) -90°ns (R9802244) -EN67 (0.65:1) (R9802243) -EN66 (0.80 - 1.21:1) (R9802003) -EN76 (0.95 - 1.30:1) (R9802242) -EN63 (1.20 - 1.70:1) * (R9802241) -EN61 (1.70 - 2.50:1) * (R9801211) -EN44 (2.50 - 4.60:1) * Standard Lens Option(s)
Décalage de la lentille optique	Up to 88% vertical lens shift & up to 38% horizontal lens shift (depending on lens selection) Visit the Barco Residential Lens Calculator for further information Download Lens & Airflow Data Here
Coupe-flux optique	Yes
Correction des couleurs	P7 RealColor™
Gamme de couleurs	DCI (P3) Color Wheel: DCI P3 T Color Wheel: REC.709 M Color Wheel: REC.709
Traitement des images	Embedded Warp & Blend Engine
WARP	4-Corner Warp & Bow Correction via Warp Engine
Orientation	360° Rotation
Connexion réseau	10/100 Ethernet via RJ45 connection
Serveur web intégré	Yes
Diagnostics	via Prospector web interface
HDR	HDR10
3D	Active Stereoscopic 3D Additional hardware required please contact an authorized Barco representative for details
Entrées	1 x HDMI™ 2.0 (HDCP 2.2) 1 x HDBaseT (HDCP 1.4 -9Gbps only) 2 x Dual Link DVI-D 2 x Display Port (1.2) 12G-SDI 1 x RJ45 Ethernet 1 x RS232 1 x Remote Control (RC) 3 x USB (2 x Rear, 1 x Front) DMX (1 x Input, 1 x Output)
Résolutions en entrée	From VGA up to 4K UHD (3,840 x 2,160) @ 60Hz or up to 2,560 x 1,600 @ 120Hz
Latence	TBD
Contrôle	IR, RS232, IP, 12v Trigger Driver modules available for: Crestron, Control4, RTI & Savant NOTE: 12v Trigger(s) do not follow standard functionality and require an IP command to enable / disable them. Download our integration guide for more information.
Alimentation électrique	100 -240V / 50 -60Hz
Consommation électrique	1,100 W -Max.
BTU par heure	4,000 BTU/h -Max.
Alimentation de secours	Standby ECO Mode: 110v -0.73W (with LAN Connection) 230v -0.82W (with LAN Connection)
Niveau sonore (habituel à 25 °C/77 °F)	36 dB(A)
Température de fonctionnement	10 to 45 °C at Sea Level Optimal Set Point: 20 °C
Humidité (fonctionnement)	20 to 80% (relative humidity)

Spécifications techniques

BALDER

Configuration minimale en matière de circulation d'air	Air Inlet (from Rear w/Feet Down): Right Side Exhaust (from Rear w/Feet Down): Rear Clearance Requirements: Front: 1cm Left: 1cm Right: 50cm Rear: 100cm Top: 1cm
Flux d'air évacué	112 ft ³ /min @ 25 °C 190 m ³ /hour @ 25 °C Download Lens & Airflow Data Here
Dimensions (L x L x H)	Excluding Lens 475 x 588 x 286 mm 18.7 x 23.1 x 11.3 in.
Poids	Excluding Lens 37 kg / 81.5 lbs
Dimensions à l'expédition	Excluding Lens 730 x 600 x 480 mm 28.7 x 23.7 x 18.9 in.
Poids à l'expédition	Excluding Lens 43 kg / 94.8 lbs
Accessoires standard	Power Cord, Remote Control
Certifications	CE, FCC Class A and cCSAus
Exigences en termes de sécurité	This projector is Risk Group 2 (RG2) according to IEC EN 62471-5. This projector may become Risk Group 3 (RG3) when an interchangeable lens with throw ratio greater than 4.7 is installed. For Northern America, installation requirements according to Risk group 3 (RG3) must be followed when interchangeable lens with throw ratio greater than 2.5 is installed. Refer to the installation manual for further information.
24/7 operation	This projector is designed and warranted for heavy duty 24/7 operation. Specific measures and design considerations have been made in order for it to comply with stringent requirements in challenging applications.
Garantie	Limited 3 years parts and labor Extendable up to 5 years
*	Firmware upgradable Please contact an authorized Barco representative for details

Crée le : 27 Mar 2024

Les spécifications techniques sont susceptibles d'être modifiées sans préavis. Veuillez consulter les dernières informations disponibles sur www.barco.com.