

# TransForm NSD-430

Single Display video wall controller



TransForm NSD-430 is a compact video wall controller perfectly suited for monitoring both baseband and networked video sources. It enables customers to capture sources (networked sources, local HDMI and DP) from anywhere, and display them with high resolution 3D images on a video wall in combination. The flexibly configurable TransForm NSD-430 can either be used as a standalone video wall controller, powered by Barco's CMS control room management software, or act as a perfectly integrated display node for a video wall in a networked TransForm N solution.

As a fully qualified platform for Barco's advanced CMS control room management system, TransForm NSD-430 allows organizing display content (including 3D-accelerated) in a smart way to enhance awareness and improve decision-making.

### **Possibility to integrate into networked visualization system**

TransForm NSD-430 can be used as a display controller running all types of Windows 10 based local applications and at the same time being part of a TransForm N networked visualization system, capable of controlling multiple video walls. This offers customers a complete data overview, while providing them with interaction and collaboration possibilities. As such, information can be shared between multiple sites, making crucial information omnipresent throughout your organization and beyond.

### **Available configurations**

TransForm NSD-430 is available in several types of freely configured configurations:

- As a standalone single display video wall controller, running the full CMS Control room Management system in a single box.



- As a Single Display node in a TransForm N installation, running only the client parts of CMS on the NSD-430, and being part of a centrally managed TransForm N installation.
- As an Application Node in a TransForm N installation, where the graphical output of any Windows applications is transferred over the network to TransForm N Display Nodes.
- CMS control room management software
- Large Windows 10 desktop
- High-end 3D graphics acceleration
- Up to 16 4K-UHD outputs
- Suitable for 24/7 operation
- High input density
- Universal IP streaming video decoding
- Baseband capture cards for DisplayPort and HDMI
- Local application support
- Latest Intel (R) Core (TM) Xeon core processor for concurrent application processing and software-based media decoding

**Product specificaties****TRANSFORM NSD-430**

General specifications	
Geheugen	32/64/128/256 GB
Netwerk	2x 1Gb/s LAN
Processor	Intel(R) Xeon Silver 4310 12-core processor 2.10 GHz
Harde schijf	2x 480 GB Solid-State Disk SSD (Raid-1), or 2x 960 GB Solid-State Disk (Raid-1)
Uitgang	Up to 16 4K-UHD displays Up to 64 HD displays, using Barco loop-through capable displays
Invoer	Up to 5x 2ch DP1.2 input cards (supporting resolutions up to 4096x2160 @60Hz) Up to 5x 2ch HDMI 2.0 (2x4K -HDCP not supported) Up to 4x 4ch HDMI 1.4 (4xHD -HDCP not supported) Up to 4x 4ch HDMI 1.4 (4xHD -HDCP supported) Up to 4x 1ch HDMI 2.0 (1x4K -HDCP supported)
Vormgeving	4U 19" Rackmount housing
Afmetingen	Without handle: 482 mm (W) x 177 mm (H) x 472 mm (D)   19 in x 6.9 in x 18.58 in
Gewicht	19 -25 kg (without packaging)   41.89 -55.12 lbs
Temperatuurbereik	Operating temperature: 0° -35°C   32° -95°F Storage temperature: -20° -60°C   -4° -140°F
Vochtigheid	5% -80% (non-condensing)
Geluidsniveau	Max. 49dbA (measured at 1m / 32.8ft distance at 25°C / 77°F)
Naleving	CE, CB, UL, FCC Class A
Streaming video standards	H.264, MPEG2/4, MxPEG, MJPEG, V2D, H.263, VNC, ProServer (with HDCP support on HDMI ports) - For all supported codecs see our continuously extended reference list of supported encoders -For supported number of sources see VCORE Check tool

**Laatst bijgewerkt: 12 Apr 2024**

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg [www.barco.com](http://www.barco.com) voor de meest recente specificaties.