

# TruePix TP0.9-Q

适用于中等亮度应用的 0.9 毫米像素间距、高分辨率室内 LED 显示屏



- 智能工程保证真正无缝的结果
- 全天候流畅高效的运行
- 在各种照明条件下都能提供出色的色彩准确度
- 减小环境影响
- 最长可达 5 年的专属服务与支持

TruePix TP0.9-Q 是巴可公司的全新旗舰室内高分辨率 LED 平台。27.5 英寸的显示单元具有 16:9 纵横比，低至 0.9 毫米的像素间距。TruePix 专为控制室、企业和广播可视化应用而设计，适用于强环境光的场景或是环境光受控较暗场合

## 真正无缝的结果

TruePix 基于数十年的经验为 LED 拼接显示系统体验树立了新标准。该解决方案通过将智能工程与下一代 Infinipix<sup>®</sup>，即 Infinipix<sup>®</sup> Gen2 相结合，确保在真正无缝的可预期的条件下展示栩栩如生的画面效果。保证全天候运营顺畅高效，让您完全放心。

巴可 TruePix 的智能工程引入了独特的机械概念，实现了无风险的精确安装，消除了视觉失真。这种无与伦比的无缝和平整度是通过半自动引导式模块导入和机械自悬浮系统来实现的。下一代巴可专有的 Infinipix<sup>®</sup> 处理功能，即，Infinipix<sup>®</sup> Gen2，可以保证在任何亮度水平下的图像完整性，以及卓越的颜色精度。它可以灵活、自动地支持任何内容需求，同时减少眼睛疲劳。

## 随时安心

通过不间断的数据流保证全天候平稳高效运行。用户可以通过使用节能待机模式来减少碳足迹。长达 5 年的专门服务和支持（确保统一的观看体验），让您在整个产品生命周期内都高枕无忧。

**技术规格****TRUEPIX TP0.9-Q****LED tiles**

Pixel pitch	0.953
Pixel per module	640x360 (HXV)
Aspect ratio	16:9
LED lifetime	100,000h (video -50% brightness)
Brightness	>600 nit
Peak brightness	780 nit
Internal processing	23 bit
Color depth	16 bit (281 trillion colors)
Shaders	No
Control	Infinipix® Gen2
Refresh rate @60Hz	3,840 Hz
3D	3D supported
Frame rate	24 -144 Hz
Hor. viewing angle	160° +/-5°
Vert. viewing angle	160° +/-5°
Brightness uniformity	>98%
Dimming	0-100%
Contrast	>7,000:1
Power consumption	766W/m <sup>2</sup> 160 W/Tile (max) 280 W/m <sup>2</sup> 58 W/Tile(typ)
Heat dissipation	2,611 BTU/h/m <sup>2</sup> (max) 955 BTU/h/m <sup>2</sup> (typ)
Ceiling configurations supported?	Yes
Heat dissipation front/back	54%/46%
Operation power voltage	AC power: 100-240V 50/60Hz DC power: Input: 36-55Vdc 16A (max.) Output: 36-55Vdc 10.72A/36V (max.) or 12.55A/55V (max.)
Operational humidity	10 -80%
Operational temperature	-10°C to +40°C / 14°F to 104°F
Storage temperature	-20°C to +60°C / -4°F to 140°F
Storage humidity	10 -80%
Redundancy	Power: Optional Standard on REM tiles Data: Standard Inter-tile redundancy Embedded signal loop redundancy Optional N + N redundancy
HDR	HLG / HDR10 supported
Concave curvature	Up to 5° standard curved tile (7m radius) Up to 5° curved modular tile (3.5m radius)
Convex curvature	Up to 3° standard curved tile (12m radius)
Ceiling configurations supported?	Yes
Dimensions	(WxHxD) 609.92x343.08x71mm / 24.01"x13.5"x2.80"
Weight	Standard / curved tiles: 8.3kg/tile (single PSU) / 8.7kg/tile (dual PSU) Modular curved tiles: 9.1kg/tile (single PSU) 9.5kg/tile (dual PSU)
Serviceability	Full front & full back service Modular curved tile -Full front & full back service (PSU only back access)
Cable management	No external cabling
Installation	Self-leveling with surface tolerance compensation
Module replacement	Automated parallel motorized extraction
Module placement	Guided module placement
Ergonomics	SteadyView™ driver algorithm to reduce eye fatigue
Certifications	CE, UL, FCC class A, RoHS, WEEE, REACH, CCC, RCM
TAA Compliance	Not available
Warranty	3 years
EssentialCare Service offering	5 years with LED batch compatible modules

生成于: 30 May 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看[www.barco.com.cn](http://www.barco.com.cn)以了解最新规格。