


# Laser Screen 2.4

Designed to amplify the full potential of laser projection by Barco



- **Enhanced appearance**
- **Precision sharpness**
- **Even better uniformity**
- **Both 2D and 3D**
- **Efficient Sustainability**

The new Barco Laser Screen 2.4 has been designed to complement and enhance Laser Projection by Barco. The laser-matched pair work in harmony to enhance and elevate what's visually possible. The new Barco Laser Screen 2.4 has been designed to complement and enhance Laser Projection by Barco. The laser-matched pair work in harmony to enhance and elevate what's visually possible. The new Barco Laser Screen 2.4 has been designed to complement and enhance Laser Projection by Barco. The laser-matched pair work in harmony to enhance and elevate what's visually possible. The new Barco Laser Screen 2.4 has been designed to complement and enhance Laser Projection by Barco. The laser-matched pair work in harmony to enhance and elevate what's visually possible.

## **Cinematic brilliance**

Elevate your cinematic experience to unprecedented heights with the Barco Laser Screen 2.4. Crafted through years of industry-leading expertise, extensive cinema knowledge, and in-house innovation, this screen is precision designed to amplify the full potential of laser projection in today's cinema landscape.

## **Laser performance**

When you pair the new screen with Laser Projection by Barco, the result is an unparalleled visual performance – that you and your audiences will notice.

The marriage of the best laser projection technology with the Barco Laser Screen 2.4 delivers laser-powered movie experiences at a new level in both 2D and 3D.

## **Experience**

Designed and tested by cinema experts, the new Barco cinema screen will delight moviegoers around the world.

**Product specificaties****LASER SCREEN 2.4**

General specifications	
Gain	2.4: 23°HGA
Signal to noise ratio	220+
Perforation	Micro-perforated (3.5% void)
Surface	Textured PVC with High Gain Coating
Material width	54" – 1.4 m
Thickness	Approx. 0.0154" – 0.39 mm
Weight	Approx. 0.0154" – 0.39 mm
Fire retardancy	NFPA-701, M3, BS 5867 Part 2: 2008 Type B, B1 Please contact us for additional certification requirements
Edging	PVC grommets every 9 inches center to center Pipe pockets, Velcro, snaps and other edging options available upon request
Packaging	Rolled on a cardboard tube into a highly resistant carton
Warranty period	24 Months

Laatst bijgewerkt: 13 May 2024

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg [www.barco.com](http://www.barco.com) voor de meest recente specificaties.