

iCon H500

Network-centric, 1080p HD, 5,000 lumens, single-chip DLP projector



Especificações técnicas

ICON H500

Especificações gerais

Saída de luz	5000 ANSI lumens
Resolução	1920 x 1080 (native)
Uniformidade de brilho	> 95% for the total screen
Lâmpada	2x 250 Watt P-VIP lamp in lamp housing, pre-aligned for max. light output. Typical lifetime: 1,500 h/lamp
Ótica	Sealed optical engine
Razão de contraste	> 2000:1 (full white/full black; depending on lens, focus and projector settings)
Visor	1-chip 0.95" DarkChip3® DLP™ 1080p panel with BrilliantColor™ processing and a native HDTV resolution of 1920 x 1080 pixels, 16:9 aspect ratio
Roda de Cores	RGBW
Recursos	<ul style="list-style-type: none">▪ Advanced picture-in-picture (PiP)▪ Intelligent dual lamp system▪ On board PC with Windows OS for network centric operation▪ Advanced desktop integration (source and PiP handling through Windows OS)▪ Sealed optical engine▪ Standard cable basket
Entradas	<ul style="list-style-type: none">▪ 1x Component video, RGBHV, RGBS or RGSB (5x BNC)▪ 1x Composite video (BNC)▪ 1x S-video (4-pin mini-DIN)▪ 1x VGA (D15 connector)▪ 2x DVI-D (Digital Visual Interface-Digital)
Saídas	<ul style="list-style-type: none">▪ 1x DVI-D
Compatibilidade	<ul style="list-style-type: none">▪ All current video sources in composite, S-video, component or RGB formats▪ All current HDTV sources (720p, 1080i)▪ All computer graphics sources with a pixel clock up to 270 Mhz (VGA, S-VGA, XGA, SXGA, SXGA+, UXGA, QXGA: 2048x1536)▪ DVI sources up to UXGA and HDTV resolution▪ Apple Macintosh formats
Frequências de Varredura	Horizontal 15kHz -140kHz Vertical 25Hz -150Hz
Comunicação	<ul style="list-style-type: none">▪ 1x D9 connector for RS-232▪ 1x IR remote receiver▪ 4x USB▪ 1x RJ45 ethernet▪ 1x PCMCIA slot (Type II)
Tamanho da tela	From 1.2 -6m / 4 -20ft
Deslocamento de Lente	Max. vertical shift from -25% to +140% (with QCLD 0.85:1 lens: +/-25%)
Servidor de vídeo integrado	<ul style="list-style-type: none">▪ Pentium M 1.6 GHz processor▪ 1 GB RAM▪ 40 GB harddisk (5,400 rpm)▪ Microsoft™ Windows XP™ Professional Multi-language OS installed▪ Barco Server software for network communication between display server and clients▪ DropZone software▪ Proximity Desktop client software▪ Remote Control & Diagnostics software
Consumo de energia	Max. 730 Watt
Energia de CA	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
Regulamentos de Segurança	Compliant with ETL60950 and EN60950
Interferência Eletromagnética	Compliant with FCC rules & regulations, part 15 CE EN55022 Class A and CCC
Dimensões	Projector body with cable basket: W 415 mm (16.34") x H 195 mm (7.68") x D 565 mm (22.24") Without cable basket: D = 487 mm (19.17") Including lens: Dmax = 590 mm (23.23")
Peso	Net weight, body only: 16 kg (35.3 lbs) Shipping weight: max. 20 kg (44.1 lbs)

Gerada em: 09 Jul 2024

© 2024 Barco nv. Todos os direitos reservados. A reprodução total ou parcial sem permissão por escrito é proibida. Todos os nomes de marca e produto são marcas comerciais, marcas comerciais registradas ou nomes dos respectivos proprietários. Por causa da inovação contínua, as informações e as especificações técnicas estão sujeitas a alterações sem aviso prévio. Verifique www.barco.com para obter as especificações mais recentes.