

# OSRAM 3000W XBO DHP L OFR



**Product specifications****OSRAM 3000W XBO DHP L OFR**

General specifications	
Supplier	OSRAM
Supplier order numbers	XBO 3000 W/DHP L OFR
Warranty hours	1,700 hours

Last updated: 15 Mar 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.