


Atlas

Compact mechanical system designed to house Poly-Silicon LCD projection systems with XGA or SXGA resolution and different screen types in 67" or 84" diagonal.



Product specificaties

ATLAS

General specifications

Wisselstroom	95-230 VAC $\pm$ 10%, 50-60 Hz
Helderheidsuniformiteit	> 95 %
Compatibiliteit	Barco's Atlas integrates with the existing network environment and video sources via BARCO's graphical control units: EOS Compact, Power and Ultra, Hydra and Visu+.
Contrast	250:1
Afmetingen structuur	Atlas 67" -XGA • Width 1368 mm / 53.86 in. • Height 1026 mm / 40.39 in. • Footprint 753 mm / 29.65 in. • Depth 897 mm / 35.32 in. • Socket height (min) 614 mm / 24.17 in. • Socket height (max) 1288 mm / 50.7 in. • Weight 108 kg / 238 lbs Atlas 67" -SXGA • Width 1335 mm / 52.56 in. • Height 1068 mm / 42.05 in. • Footprint 798 mm / 31.4 in. • Depth 942 mm / 37.1 in. • Socket height (min) 492 mm / 19.4 in. • Socket height (max) 1288 mm / 50.7 in. • Weight 108 kg / 239 lbs Atlas 84" -XGA • Width 1708 mm / 67.24 in. • Height 1281 mm / 50.43 in. • Footprint 1041 mm / 41 in. • Depth 1186 mm / 46.68 in. • Socket height (min) 486 mm / 19.13 in. • Socket height (max) 1288 mm / 50.7 in. • Weight 138 kg / 305 lbs Atlas 84" -SXGA • Width 1650 mm / 65 in. • Height 1320 mm / 52 in. • Footprint 1079 mm / 42.5 in. • Depth 1225 mm / 48.2 in. • Socket height (min) 366 mm / 14.4 in. • Socket height (max) 1288 mm / 50.7 in. • Weight 138 kg / 305 lbs
Naleving van milieuwetgeving	• Operating temperature: 17 °C -27 °C or 62 °F -80 °F • Humidity: recommended 40% -60%, non condensing Typical for stitched screens. Consult download for more info on screen modules.
Lamp	100 Watt lamp Operation time 8,000 hours (average)
Lcd-panelen	• XGA with 3-panel Poly-Silicon LCD, 4:3 • SXGA with 3-panel Poly-Silicon LCD, 5:4
Luminantie	Atlas 67" XGA -130 cd/m ² 38 ftL Atlas 67" SXGA -110 cd/m ² 32 ftL Atlas 84" XGA - 262 cd/m ² 77 ftL Atlas 84" SXGA -220 cd/m ² 65 ftL
Lichtstroom	XGA -500 lumens SXGA -600 lumens
Optioneel	All projector settings are accessible through Barco's wall management software. Full features of this software can be viewed under this website 'Application software'
Energieverbruik	XGA resolution -140 W SXGA resolution -220 W
Resolutie	XGA -1024x768 pixels SXGA -1280x1024 pixels depending on the projector, screen type and size used
Schermafmeting	• 67" or 84" diagonally • High gain screens for high brightness and high contrast black screens for wide viewing angles • Other screens on request • Download the brochure for more info on the principles and technologies

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

www.barco.com

BARCO