

# OverView cPG84 (Atlas C4)

84" Display Wall system integrating 3-panel Poly-Silicon LCD technologie with XGA resolution.



## 技术规格

## OVERVIEW CPG84 (ATLAS C4)

### 一般规格

|       |   |
|-------|---|
| 分辨率   | XGA   |
| 宽高比   | 4:3   |
| 颜色    | 16.7 millions   |
| 灯泡    | <ul style="list-style-type: none"><li>· 100 Watt lamp</li><li>· operation time 8,000 hours (average)</li></ul>  |
| 电源    | 95-230 VAC ± 10%, 50-60 Hz  |
| 电源    | 140 W   |
| 亮度    | 262 cd/m <sup>2</sup>   76 ftL  |
| 亮度    | 600 lumens  |
| 对比度   | 250:1   |
| 亮度均匀性 | > 95%   |
| 尺寸结构  | <ul style="list-style-type: none"><li>· Diagonal 84"</li><li>· Width 1708mm / 67.24 in.</li><li>· Height 1281mm / 50.43 in.</li><li>· Footprint 1041mm / 41 in.</li><li>· Depth 1186 mm / 46.68 in.</li><li>· Socket heighth 486 mm / 19.13 in.</li></ul> |
| 运行环境  | <ul style="list-style-type: none"><li>· Operating temperature: 17 °C -27 °C or 62 °F -80 °F</li><li>· Humidity: recommended 40% -60%, non condensing</li></ul> Typical for stiched screens.   |
| 屏幕    | <ul style="list-style-type: none"><li>· high gain screens for high brightness and high contrast black screens for wide viewing angles</li><li>· other screens on request</li></ul>  |

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看[www.barco.com.cn](http://www.barco.com.cn)以了解最新规格。