

Barco Optix Cinemascope



The Barco Optix Cinemascope projector takes the exceptional 2.37:1 native DLP chipset used in the Barco Orion Cinemascope to the next level. This higher resolution required our optical engineers to develop all new optics and lenses, custom designed with aspherical glass elements and enhanced low dispersion glass for the highest possible image quality, increased contrast, improved color saturation and, above all, excellent sharpness.

Specifiche tecniche

BARCO OPTIX CINEMASCOPE

Specifiche generali	
Tipo di proiettore	single chip DLP® projector LVDS DMD™ with DC4 DMD™
Risoluzione	2560x1080
Emissioni luminosa	Up to 4,500 lumens
Rapporto di contrasto	Up to 8,000 : 1
Intervallo obiettivo	*0.61 : 1 (EN47), 0.8 : 1 (EN 42), 0.75 -1.13 : 1 (EN45 & EN46) 1.2 -1.7 : 1 (EN 43), 1.7 -2.5 : 1 (EN41), 2.5 -4.6 : 1 (EN 44)*
Spostamento obiettivo ottico	adjustable: vertical and horizontal, depending on lenses
Lampade	2 x 300W UHP VIDI
Durata lampada (tipica)	Up to 2,000 hours (Full power) / Up to 2,500 hours (Eco mode)
Trasporto con lampada	yes
Elemento centrale DLP™ sigillato	standard
Compatibilità	*HDTV (1080p, 1080i, 720p), EDTV (576p, 480p), SDTV (576i, 480i), NTSC, PAL, SECAM, progressive scan*
3D	*active eyewear (optional), 2x optix cinemascope(stacked): INFITEC EX® 3D and Active Stereo IR, RF models, DLPLink™
Ingressi	*2 x DVI-I, 2 x HDMI 1.3a, 2 x VGA 1 x Component, 1 x S-video*
Controllo	*1 x RJ-45 TCP/IP, 1 x 9-pin D-SUB RS232, 2 x 12V programmable trigger (3.5mm mini jack), 1 x Wired Remote 3.5mm mini jack, 2 x USB AMX Device Discovery, Crestron Certified Partner*
Alimentazione CA	8.4A ~100-240V 50-60Hz, typical consumption: Max 815W@100V
Consumo energetico	630W
Intervallo temperature in funzionamento	10 -40 °C
umidità in funzionamento non condensata	20 -80% RH
Dissipazione BTU	less than 3,109
Installazione	table top, ceiling mount, straight down or up.
Dimensioni (PXLXA)	510 x 376 x 223 mm excluding lens
Peso	12.7 kg, shipping weight 20 kg
Dimensioni con imballo	780 x 520 x 370 mm (WxHxD)
Colore alloggiamento	black and white
Certificazioni	CCC, cCSAus, FCC Class A, cUL, UL and CE
Garanzia	*limited 3 years warranty. Up to five years extended warranty available. Conditions apply.*

Generato il: 09 Jul 2024

© 2024 Barco nv. Tutti i diritti riservati. La riproduzione totale o parziale è proibita in assenza di autorizzazione scritta. Tutti i nomi di marchi e di prodotti sono marchi, marchi registrati o nomi commerciali dei rispettivi proprietari. A causa delle continue innovazioni, le informazioni e le specifiche tecniche sono soggette a modifiche senza preavviso. Controlla www.barco.com per le specifiche più recenti.

