

# SLM G10 Performer

A compact and Powerful Projector for Rental & Staging Applications.



**技术规格****SLM G10 PERFORMER**

一般规格	
光输出	10,000 ANSI Lumen
分辨率	1024 x 768 (native) 1600 x 1200 (max)
分辨率	1024 x 768 (native) 1600 x 1200 (max)
数字微镜器件	3 high resolution XGA DMD™s
亮度均匀性	90 %
对比度	Normal mode: 500 : 1 High mode: 1000 : 1 (Full White/Full Black)
灯泡	Lifetime (max): 1000 Hrs Lifetime (typ): 500 Hrs  Lamp power: 2,2 kW
噪音级别(@ 20°C -68°F)	< 56
噪音等级 (@ 40°C -104°F)	< 58
电源电压	200-240 V
功率消耗	2750 W
环境温度	35°C (95F)
尺寸	875 mm x 585 mm x 429 mm 34,5" x 23" x 16,9"
重量 (包括装备齿轮)	57 kg (126 lbs)
镜头	BARCO's "click-and-play™" TLD lenses provide the highest quality picture. Available both in fixed and zoom versions.
镜头移动	Motorized V shift: up to 118% Motorized H shift: up to 65%
封装DLP™内核	No
无缝切换	Standard
ScenergiX	Standard
网络连接	Optional
固定输入	· 2 Multifunctional 5-cable inputs for the connection of RGB analogue signals with standard sync (BNC connectors) or tri-level sync, sync on green or separate sync, Standard Video signals, S-VHS signals  · 2 Multistandard DVI  · SDI input (Serial Digital Input)
可选输入	One free digital input slot for optional input modules:  · SDI · HD -SDI
远程控制	· RS232 or RS422 loop-through input (D9-connector) for PC based projector control  · Communication input (D9-connector) for peripherals  · 3 pin male XLR connector for wired remote (standard remote)  · 3 pin female XLR connector for bi-directional communication (rugged remote)

**生成于: 16 Mar 2023**技术规格随时变化, 不会事先通知。请访问[www.barco.com.cn](http://www.barco.com.cn), 获取更新信息。