


Hodr

Hodr has a pleasing calm uniform image and is designed for large screens or high ambient light environments.



- Theatre & Media room Series
- 4K UHD Resolution (3840 x 2,160)
- 3-Chip DLP
- Up to 7,500 ANSI Lumens

Hodr delivers perfect cinematic colors, supporting DCI/P3 color gamut.

Our Hodr features a pleasing and uniform image with the power light up medium to large screens, whilst delivering an unbelievably detailed image with spectacular color fidelity for an unmatched experience that will delight even the most discerning clients.

Single Step Processing SSP™

Pulse is a hardware and software based platform that simplifies the signal allowing it to transmit from source to screen much faster and more efficiently. We use an advanced image processing technique to display the image on the screen without any artefacts and with the lowest possible processing lag (<20ms with all image processing), this is made possible by our Single Step Processing (SSP™).

State of the art electronics

All new Pulse electronics have been designed to process 4K with HDMI™ 2.0a and HDCP 2.2 and the optical engine utilises the very latest 0.9" DMD DLP chipset, delivering 3,840 x 2,160 pixels to screen. Hodr also features HDR, motorised lenses and Barco's unique RealColor processing, enables simple and accurate calibration to any desired color standard or white point.

Building Blocks

Hodr offers 4K UHD resolution (3,840 x 2,160) for superb image quality. Thanks to its modular design of only five building blocks, Hodr is easy to service.

Laser Light Source

Outstanding image quality also requires an exceptional light source which is why we designed Hodr with a brand new laser engine, significantly improving image uniformity (95%) over its predecessor. Hodr uses custom selected lasers to secure that we can deliver DCI/P3 color gamut.

Lasers last longer than traditional projector lamps, are not as fragile and offer nearly instant on/off.

Spécifications techniques**HODR**

Spécifications générales	
Type de projecteur	Three chip DLP
Technologie	3 x 0.90" DMD™ with sealed core
Résolution	3,840 x 2,160 (4K UHD)
Rapport d'aspect	1.78:1 (16:9)
Source lumineuse	Laser phosphor
Durée de vie de la source lumineuse	Up to 20,000
Luminosité	Up to 7,500 ANSI Lumens Dimable to 4,000 lumens
CLO (constant light output/sortie lumineuse constante)	Yes
Taux de contraste	20,000:1 (with DynaBlack enabled) 2,000:1 Sequential 600:1 ANSI
Uniformité de la luminosité	>90%
Gamme de lentilles	(R9801661) -TLD+ (0.41:1) -90 Degree Lens (R9862001) -TLD+ (0.73 - 0.94:1) -90 Degree Lens (R9801414) -TLD+ (0.92 - 1.33:1) (R9862005) -TLD+ (1.24 - 1.56:1) (R9862010) -TLD+ (1.49 - 2.02:1) * (R9862020) -TLD+ (2.01 - 2.76:1) * (R9862030) -TLD+ (2.69 - 4.41:1) * (R9862040) -TLD+ (4.37 - 7.35:1) * (R9829997) -TLD+ (6.95 - 10.83:1) * Standard Lens Option(s)
Décalage de la lentille optique	Up to 73% vertical lens shift & up to 28% horizontal lens shift (depending on lens selection) Visit the Barco Residential Lens Calculator for further information Download Lens & Airflow Data Here
Coupe-flux optique	Yes
Correction des couleurs	P7 RealColor™
Gamme de couleurs	Up to DCI (P3)
Traitement des images	Embedded Warp & Blend Engine
WARP	4-Corner Warp & Bow Correction via Warp Engine
Orientation	360° Rotation
Connexion réseau	10/100 Ethernet via RJ45 connection
Serveur web intégré	Yes
Diagnostics	via Prospector web interface
HDR	HDR10
3D	Active Stereoscopic 3D Additional hardware required please contact an authorized Barco representative for details

Spécifications techniques

HODR

Entrées	1 x HDMI™ 2.0 (HDCP 2.2) 2 x HDBaseT (HDCP 1.4 -9Gbps only) 1 x Display Port 1.2 Quad 3G / 12G SDI / BarcoLink 1 x RJ45 Ethernet 1 x RS232 1 x USB 2 x DMX (1 x Input / 1 x Output) 1 x XLR for Wired Remote 2 x 3D Sync (1 x Input / 1 x Output) Optional Upgrade: Quad DP1.2
Résolutions en entrée	HDMI™: Up to 4,096 x 2,160 @ 24/25/30/50/60Hz DisplayPort (Single Input): Up to 4,096 x 2,160 @ 24/30/50/60Hz via Optional Quad DP1.2 Input Card DisplayPort (Layout Mode: 2 x 2) *: Up to 1,920 x 1,080 @ 120Hz Up to 2,048 x 1,080 @ 120Hz DisplayPort (Layout Mode: 4 x 1) *: Up to 960 x 2,160 @ 120Hz * Specialist GFX cards may be required
Latence	TBD
Contrôle	IR, RS232, IP, 12v Trigger Driver modules available for: Crestron, Control4, RTI & Savant WiFi (Optional), XLR Wired Remote, GSM (Optional)
Alimentation électrique	110 -130V / 200 -240V / 50 -60Hz
Consommation électrique	110V: 1,321W Max, measured in 20-25°C / 68-77°F 230V: 1256W Max 20-25°C / 68-77°F Power consumption will increase if ambient temperatures increases above 25°C / 77°F
Niveau sonore (habituel à 25 °C/77 °F)	43 dB(A)
Température de fonctionnement	0 to 40 °C at Sea Level Optimal Set Point: 20 °C
Humidité (fonctionnement)	0 to 80% (relative humidity)
BTU par heure	Max. 4,288 BTU/h @ 200 -240V Max. 4,516 BTU/h @ 110 -130V
Configuration minimale en matière de circulation d'air	Air Inlet (from Rear w/Feet Down): Front / Top / Right Exhaust (from Rear w/Feet Down): Rear Clearance Requirements: Front: 40cm Left: 1cm Right: 40cm Rear: 40cm Top: 40cm

Spécifications techniques**HODR**

Flux d'air évacué	152 ft ³ /min @ 25 °C 258 m ³ /hour @ 25 °C Download Lens & Airflow Data Here
Dimensions (l x L x H)	Excluding Lens 540 x 725 x 355 mm 21.26 x 28.54 x 14 in.
Poids	Excluding Lens 48kg / 105bs
Dimensions à l'expédition (l x L x H)	Including Pallet -Excluding Lens (Packaged Separately) 850 x 665 x 613 mm 33.46 x 26.18 x 24.13 in.
Poids à l'expédition	TBD
Accessoires standard	Power Cord / Remote Control
Certifications	CE, FCC Class A and cCSAus
Exigences en termes de sécurité	This projector may become Risk Group 3 (RG3) when an interchangeable lens with throw ratio greater than 2.3 is installed. Refer to the installation manual for further information.
Garantie	Limited 3 years parts and labor Extendable up to 5 years
*	Firmware upgradable Please contact an authorized Barco representative for details

Crée le : 27 Mar 2024

Les spécifications techniques sont susceptibles d'être modifiées sans préavis. Veuillez consulter les dernières informations disponibles sur www.barco.com.