

Infinipix[®] IND-100

Infinipix[®] Dual EyePoint processor for LED displays



- **Manages one or more connected display(s)**
- **Fine-tunes brightness without any loss of image quality**
- **Allows for brand-specific color calibration**
- **Smooth and seamless results for still and moving content**
- **Supports Dual Eye Point Technology**

The InfiniPix[®] IND-100 is an addition to Barco's second generation of LED display processors. The IND-100 processes signals coming from connected video sources and transmits them to the Infinipix[®] transceiver cards integrated into the LED tiles. This special version of the Infinipix[®] INP-100 is designed to extend the 3D Stereo capabilities for Dual Eye Point applications.

Delivering flawless viewing experiences


Whatever your needs are, the Infinipix[®] Gen2 platform helps you get the most out of your LED content.

Whether your application requires a dimmed LED wall or a display run at high-brightness, you can keep the same color accuracy, grey scale levels and details thanks to the Infinipix[®] Gen2 processing. Don't let your creativity be limited by your canvas, and always show your content as intended.

With lowest latency for showcasing motion content, black frame insertion to optically reduce motion blur and premium anti-aliasing filters to realize perfectly scaled and sharp images, Barco's Infinipix[®] Gen2 is optimized to bring state-of-the-art results and exceptional viewing experiences for still, slow-moving and fast-moving content.

Adding 3D Stereo specific capabilities

When users require 3D stereo capabilities on the LED Wall, the IND-100 is the



When users require 3D stereo capabilities on the LED Wall, the IND-100 is the preferred controller choice. Having 2 DP input connectors gives the customer the freedom to drive the LED wall with either an active stereo sequential source or by combining both left eye and right eye video signals. Furthermore, the controller also allows to combine 2 active stereo sources at 120Hz to be combined to a 240 Hz output. This gives the customer the capability to use the LED wall with 2 points of view in a virtual environment, also called 'Dual Eye Point' feature.

技術仕様

INFINIPIX® IND-100

一般仕様

3D同期	Implemented on BNC connector
ウォール制御	1x GbE RJ-45 connector used as link to a separate Video wall Manager Edge for centralized management
ビデオ出力	8x SFP Modular Wall Outputs: SFP+ cages only supporting the Barco included Finisar SFP modules Using multi mode fiber of minimum type OM3 within the OM specified length
ビデオ入力	2x Displayport 1.4: · Up to 7680x4320@30, YCbCr 4:2:2 at 12bpc (36 bit/px) · Up to 3840x2160@60Hz RGB, or YCbCr 4:4:4 at 12 bpc (36 bit/px) · Up to 3840x2160@120Hz, YCbCr 4:2:2 at 12bpc (36 bit/px) with custom timings · Up to 2560x1600@120Hz RGB, or YCbCr 4:4:4 at 12 bpc (36 bit/px) Input capabilities: · Progressive RGB and YCbCr 4:2:2 and 4:4:4 · Supports input bit depth of up to 12 bpc · Refresh frequencies: 23.98 Hz, 24 Hz, 25 Hz, 29.97 Hz, 30 Hz, 47.95 Hz, 48 Hz, 50 Hz, 59.94 Hz, 60 Hz, 100 Hz, 119.88 Hz, 120 Hz, 144 Hz, 240 Hz (Please consult your LED panel specification for its supported frequencies which may be different than what is supported by the processor)
3Dステレオオプション	1 x Sequential 3D stereo input @120 Hz on 1 of the DP1.4 inputs 2 x Passive stereo (left / right eye mono) @ 60Hz on 2 DP1.4 inputs combined to 120 Hz output 2 x Sequential 3D stereo (user 1 & user 2) @120 Hz on 2 DP1.4 inputs combined to 240 Hz
高度低気圧	Max. 2000 m (6562 ft)
規制遵守	CE, CEBEC, cSGSul, FCC
環境温度	Operational: 0-40°C Celsius (32-104°F) Non-operational: -20°C -60°C (-4°F -140°F)
環境湿度	Operational: 10%-85% @ 40°C / 104°F non-condensing Non-operational: 10%-95% @ 40°C / 104°F
寸法 (高さx幅x奥行き)	177 x 222.2 x 43.5 mm / 7 x 8.75 x 1.7 in
重量	2.7 kg / 5.95 lbs
消費電力	40 Watt
電源	100-240VAC, 1.5A -0.8A -50/60Hz
保証	3 years standard warranty

生成日:03 Oct 2024

© 2024 Barco nv.(C) Barco. All rights reserved. (無断転載を禁ず。) 書面による許可なく全部または一部を複製することは禁止されています。すべてのブランド名および製品名は、それぞれの所有者の商標、登録商標、または商号です。継続的な技術革新により、情報および技術仕様は予告なく変更される場合があります。最新の仕様についてはwww.barco.comをご確認ください。