

# BARCOData 708 + Iris<sup>3</sup>



## Product specifications

## BARCODATA 708 + IRIS<sup>3</sup>

### General specifications

Compatibility	Horizontal autolock scan frequency of 15-69 kHz Vertical autolock scan frequency of 37-210 Hz Standard Video, S-Video and professional Component Video RGB signals from a wide range of PC graphics boards with resolutions up to 1280 by 1024 pixels/60 Hz Wideband 75 MHz RGB amplifiers A full complement of input signal connections
Contrast	>1000:1 (full field contrast)
Light output	1100 Lumen (at 10 % peak white) 130 ANSI Lumen (Economy mode) 170 ANSI Lumen (Normal mode) 200 ANSI Lumen (Boost mode)
Screen size	Min.: 1.4 m x 1.05 m (4.6' x 3.5') Max.: 6 m x 4.5 m (20' x 15')

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.