


Bragi CinemaScope

Using Barco's renowned Pulse electronic and software platform, Bragi CinemaScope is powered by a revolutionary, new, high lumens density (HLD) RGB LED light engine.



- Theater Series
- 5K UHD Resolution (5,120 x 2,160)
- Solid State RGB LED
- Up to 2,200 ANSI Lumens

Bragi takes its name from an historical ninth-century poet. His poems were so outstandingly artful and moving that subsequent generations imagined that, upon his death, Odin had appointed him the court poet of Valhalla.

Bragi, being Balder's brother and inherits the same design philosophy, optical core and lenses.

Professional grade optics

By basing Bragi CinemaScope's optical engine on its bigger brother Balder CinemaScope's architecture, incorporating custom designed aspherical glass elements and enhanced low dispersion glass lenses, image quality is in a class of its own.

Topping that, Bragi's chassis and core are built from aluminium and magnesium, which offer exceptional robustness, resulting in the best picture quality ever shown at this level.

State of the art electronics

Thanks to our unique single step processing technology (SSPTM), Pulse electronics are designed to process 4K UHD, HDMITM 2.0a, HDCP 2.2 and HDR10 signals with extremely low latency.

Bragi CinemaScope uses the very latest 0.9" DMD DLP chipset, to display flawless 5K UHD (5,120 x 2,160 px), 2.37:1 aspect ratio images on screen.

CinemaScope

Our unique aspect ratio detection system, automatically crops and scales



content to fit the appropriate screen area, ranging from 1.78:1 to 2.39:1.

Manual cropping is also available for custom configurations such as cinemascope subtitle support, where only the top black bar (letterboxing) is removed, preserving the subtitles at the foot of the image.

Colors

Combining HLD LED illumination with regular LED colors which appear more saturated, the human eye is tricked to interpret this as richer, brighter colors than they are physically measured. Bragi also includes a motorized DCI/P3 filter for improved HDR color accuracy.

Additionally, Barco's RealColor processing enables simple and accurate calibration to your desired color gamut or white point.

Technische Daten

BRAGI CINEMASCOPE

Allgemeine technische Daten	
Projektortyp	Single chip DLP
Technologie	0.9" DMD™
Auflösung	5,120 x 2,160 (5K UHD)
Bildseitenverhältnis	2.37:1 (CinemaScope)
Lichtquelle	Solid State RGB LED
Lebensdauer der Lichtquelle	Up to 50,000 hours * Brightness mode dependent
Lichtausgabe	Up to 2,200 ANSI Lumens
CLO (Constant Light Output -Konstante Lichtausgabe)	Yes
Kontrast	1,800:1 Sequential 450:1 ANSI
Helligkeitsgleichförmigkeit	>90%
Objektivbereich	(R9802232) -EN68 (0.30:1) -Periscope Lens (requires vertical installation) (R9801832) -FLDX UST (0.41:1) -90°ns (R9802244) -EN67 (0.65:1) (R9802243) -EN66 (0.80 - 1.21:1) (R9802003) -EN76 (0.95 - 1.30:1) (R9802242) -EN63 (1.20 - 1.70:1) * (R9802241) -EN61 (1.70 - 2.50:1) * (R9801211) -EN44 (2.50 - 4.60:1) * Standard Lens Option(s)
Linsenverstellung	Up to 122% vertical lens shift & up to 40% horizontal lens shift (depending on lens selection) Visit the Barco Residential Lens Calculator for further information Download Lens & Airflow Data Here
Optischer Dowser	Yes
Farbkorrektur	P7 RealColor™
Farbskala	REC.709 DCI (P3) via internal filter
Bildverarbeitung	Embedded Warp & Blend Engine
WARP	4-Corner Warp & Bow Correction via Warp Engine
Ausrichtung	360° Rotation
Netzwerk-Verbindung	10/100 Ethernet via RJ45 connection
Integrierter Webserver	Yes
Diagnose	via Prospector web interface
HDR	HDR10
3D	Active Stereoscopic 3D Additional hardware required please contact an authorized Barco representative for details
Eingänge	1 x HDMI 2.0 (HDCP 2.2) 1 x HDBaseT (HDCP 1.4 -9Gbps only) 2 x Dual Link DVI-D 2 x Display Port (1.2) 12G-SDI 1 x RJ45 Ethernet 1 x RS232 1 x Remote Control (RC) 3 x USB (2 x Rear, 1 x Front) DMX (1 x Input, 1 x Output)
Eingangsaufösungen	From VGA up to 4K UHD (3,840 x 2,160) @ 60Hz or up to 2,560 x 1,600 @ 120Hz
Latenz	TBD
Bedienung	IR, RS232, IP, 12v Trigger Driver modules available for: Crestron, Control4, RTI & Savant NOTE: 12v Trigger(s) do not follow standard functionality and require an IP command to enable / disable them. Download our integration guide for more information.
Stromversorgungsanforderungen	100 -240V / 50 -60Hz
Stromverbrauch	570 W -Max
Geräuschentwicklung (typisch bei 25 °C/77 °F)	30 -33 dB(A) Max.
Betriebstemperatur	10 to 45 °C at Sea Level Optimal Set Point: 20 °C
Betriebsfeuchtigkeit	20 to 80% (relative humidity)
BTU pro Stunde	1,945 BTU/h -Max
Anforderungen Luftstrom	Air Inlet (from Rear w/Feet Down): Right Side Exhaust (from Rear w/Feet Down): Rear Clearance Requirements: Front: 1cm Left: 1cm Right: 25cm Rear: 25cm Top: 1cm

Technische Daten**BRAGI CINEMASCOPE**

Abgasstrom	58 ft ³ /min @ 22.9 °C 99 m ³ /hour @ 22.9 °C Download Lens & Airflow Data Here
Abmessungen (BxTxH)	Excluding Lens 450 x 482 x 255 mm 17.7 x 19 x 10 in.
Gewicht	Excluding Lens 21.5 kg / 47.4 lbs
Verpackungs-Abmessungen	Excluding Lens 464 x 679 x 773 mm 18.27 x 26.7 x 30.4 in
Versandgewicht	TBC
Standardzubehör	Power Cord, Remote Control
Zertifizierungen	CE, FCC Class A and cCSAus
Gewährleistung	Limited 3 years parts and labor Extendable up to 5 years
24/7 operation	This projector is designed and warranted for heavy duty 24/7 operation. Specific measures and design considerations have been made in order for it to comply with stringent requirements in challenging applications.
*	* Service required following 20,000 hours use Please contact an authorized Barco representative for details

Generiert am: 27 Mar 2024

Die angegebenen Informationen und Daten sind typisch für das beschriebene Gerät. Jede Spezifikation kann sich aber ohne vorherige Ankündigung ändern. Die aktuelle Version dieser Broschüre finden Sie unter www.barco.com.