

# RLM-W12

11,500 lumens, WUXGA, 3-chip DLP projector



- Standard active 3D
- Low power consumption
- BarcoLink for fast signal distribution

This product is still available in China.

Thanks to its standard active 3D capabilities, low noise level and high light output, the cost-effective RLM-W12 is a perfect fit for fixed installation in conference auditoriums, lecture halls and infotainment applications. Geared with an optional ceiling mount or stacking frame, the RLM-W12 can also be used for events. What's more, the RLM-W12 is equipped with TLD lenses, making it fully compatible with Barco's HDF, HDX and FLM projector families.

### Flawless image quality

Thanks to its 3-chip DLP image quality, the RLM generates crisp images with a better color saturation, more stability and richer contrast. Its WUXGA (1920x1200) resolution makes sure you see all important details at once.

### The most silent

Barco's RLM projectors are the most silent projectors in their range. They remove the strain of working under a constant drone of projection equipment, and make the only noticeable thing about it its image quality.

### Low power consumption

The RLM consumes less power than comparable projectors. Today, as energy conservation is an important consideration, the RLM benefits both your energy bill and the environment.

### Fast signal distribution

Our proprietary BarcoLink technology guarantees swift signal distribution between Barco's projectors and image processors. With BarcoLink, signals are distributed over

Our proprietary BarcoLink technology guarantees swift signal distribution between Barco's projectors and image processors. With BarcoLink, signals are distributed over a BNC coax cable, which is not only more durable but also enables you to lower your costs.

- 11,500 lumens light output
- 3-chip DLP technology
- Super silent projector
- Low power consumption
- WUXGA resolution
- Standard active 3D
- Better color stability & saturation
- Perfect for fixed installations
- Rental frame available
- Wide range of TLD lenses, compatible with HDX & FLM projectors
- Control over IP

**Product specificaties****RLM-W12****General specifications**

Type projector	WUXGA 3-chip DLP digital projector
Technologie	0.96" DMD™ x3
Resolutie	1,920 x 1,200
Helderheid	11,500 center lumens / 10,500 ANSI lumens*
Contrastverhouding	1,600:1 (standard) / 2,400:1 (CE)
Helderheidsuniformiteit	90%
Beeldverhouding	16:10
ScenergiX	Horizontal and vertical edge blending
Type lens	TLD+
Lenzen	(fix) 0.73:1 ; 1.2:1 ; (zoom) 1.25-1.6:1 ; 1.5-2.0:1 ; 2.0-2.8:1 ; 2.8-4.5:1 ; 4.5-7.5:1 ; 7.5-11.5:1
Optische lensverschuiving	Vertical: -70% to +120% / Horizontal: -30% to +30% on zoom lenses
Kleurcorrectie	P7
Lampen	2x400W
Levensduur lamp	1,500 hours (typical) / 2,000 hours (maximum)
Transport met lamp	Yes
Lampbehuizing, snelle vervanging	Yes, auto lamp select
Lampvervanging door klant	N/A
Lampgarantie (vervanging op locatie/in de fabriek)	120 days, 500 hours
Verzegelde DLP™-kern	Standard
Optische dowser	Standard
Picture-in-Picture	Up to two sources simultaneously
Oriëntatie	table -ceiling
WARP	preset values + custom
Geïntegreerde webserver	Yes
3D	Passive circular polarized (optional), active eyewear on Dual link DVI 120 Hz (standard)
Ingangen	2 x HDMI (HDCP 1.3); 5-BNC (RGBHV, RGBS/RGBsB;YUV); VGA (RGBHV, RGBS/RGBsB; YUV); cinch (RGBs, YUV); Composite video; S-Video; HSDI/3G HDSDI/SDI 3D dual link DVI/BarcoLink; 3D sync in/out BNC
Optionele ingangen	N/A
Invoerresoluties	From NTSC up to UXGA (1,600 x 1,200), including HDTV (1,920 x 1,200)
Max. pixelklok	165 MHz
Softwaretools	Projector Toolset
Controle	Mini-jack + IR, RS232, 12v trigger
Netwerkverbinding	10/100 base-T, RJ-45 connection
Voedingsvereisten	90-240V / 50-60Hz
Max. energieverbruik	1000W / Standby mode:
Geluidsniveau (standaard bij 25°C/77°F)	43dB(A)
Operationele omgevingstemperatuur	0-40°C / 32°-104°F
Operationele vochtigheid	0-80% (non condens)
Dissipatie BTU	max 3412 BTU/h
Afmetingen (B x L x H)	500 x 631 x 270mm / 19.69 x 24.84 x 10.63 inches
Gewicht	32kg (70.54 lbs)
Verzendingsafmetingen	(LxWxH) 830 x 669 x 448mm / 32.67 x 26.33 x 17.63 inches
Verzendgewicht af fabriek	32kg (70.54 lbs)
Standaardaccessoires	Power cord, wireless remote control, HDMI to DVI adaptor
Certificeringen	Compliant with FCC rules and regulations, part 15 Class A and CE EN55022 Class A, CE, TUV, RoHS, WEEE
Garantie	3 years standard, 4th or 5th year optional
*	+/-10%

**Laatst bijgewerkt: 09 Jul 2024**

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer [www.barco.com](http://www.barco.com) voor de nieuwste specificaties.