

Hydra

Universal Multi Video Insertion Unit



Product specifications**HYDRA****General specifications**

Dimensions	<ul style="list-style-type: none">• 19" industrial case, height in rack units: 6U• Width case: 435 mm 17.13"• Width with fixation: 482 mm 18.98"• Depth case: 562 mm 22.13"• Depth handles: 35 mm 1.38"• Height: 267 mm 10.51"
Heat dissipation	1800 BTU
Inputs	All input units have full decoding, scaling, filtering and scan conversion capabilities on board and perform these tasks independently from the other boards in the system.
Number of slots for in and output boards	16
Power consumption	550 W
Power supply	<ul style="list-style-type: none">• Number of power supplies: 4 (hot-swap, redundant)• Number of power leads: 2• Power supply: 100-240 VAC, 47-63 Hz
Weight	26 kg 57.3 lbs

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.