

BARCOData 9200



技术规格

BARCODATA 9200

一般规格

兼容性

Video sources in Composite, S-VHS, Component and RGB format
Most computer signals from PC graphics boards : CGA, EGA, VGA, S-VGA, XGA, up to 1180 x 900 pixels/60 Hz
Most Macintosh computers
Electronic workstations with a resolution up to 1180 x 900 pixels/60 Hz
Most computer sources with a pixel clock

对比度

>180:1 (on 5x4 B/W checkerboard)
>340:1 (full white/full black)

光输出

6000 Lumen full white
5000 ANSI Lumen

屏幕尺寸

Min.: 1 m x 0.75 m (3.3' x 2.5')
Max.: 15 m x 11.25 m (50' x 37.5')

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。