


Njord

Njord has a pleasing calm uniform image and is designed for large screens or high ambient light environments.



- **Theater & Media Room Series**
- **4K UHD Resolution (3,820 x 2,160)**
- **3-Chip DLP**
- **Up to 12,500 ANSI Lumens**

Njord inherits a lot from its predecessor Wodan, however, the light source and optical engine are completely redesigned, made smaller, more efficient, and most importantly optimized for perfect cinematic colors.

Njord not only offers a pleasing uniform image, it also has the power to illuminate large screens or high ambient light environments; like outdoor entertainment spaces and contemporary glass home designs. These environments will all benefit from an unbelievably bright and detailed image with spectacular color fidelity for the most demanding clients.

Single Step Processing SSPT™

Pulse is a hardware and software based platform that simplifies the signal allowing it to transmit from source to screen much faster and more efficiently. We use an advanced image processing technique to display the image on the screen without any artefacts and with the lowest possible processing lag (<20ms with all image processing), this is made possible by our Single Step Processing (SSPT™).

State of the art electronics

All new Pulse electronics have been designed to process 4K with HDMITM 2.0a and HDCP 2.2 and the optical engine utilises the very latest 0.9" DMD DLP chipset, delivering 5,120 x 2,160 pixels to screen. Njord also features HDR, motorised lenses and Barco's unique RealColor processing, enables simple and accurate calibration to any desired color standard or white point.

Building Blocks



Njord offers 4K UHD resolution for superb image quality. Thanks to its modular design Njord is easy to service. Njord is the most compact rugged projector that offers up to 12,500 lumens light output currently available. One of its most striking features is that as standard it's equipped with a fully featured-on-demand option for flexible light output between 4,000-12,500 lumens.

Laser Light Source

Outstanding image quality also requires an exceptional light source which is why we designed Njord with a brand new laser engine, significantly improving image uniformity (95%) over its predecessor. Njord is also equipped with custom selected lasers to deliver a DCI/P3 color gamut.

Lasers last longer than traditional projector lamps, are not as fragile and offer nearly instant on/off.

Product specificaties

NJORD

General specifications	
Type projector	Three chip DLP
Technologie	3 x 0.90" DMD™ with sealed core
Resolutie	3,840 x 2,160 (4K UHD)
Beeldverhouding	1.78:1 (16:9)
Lichtbron	Laser phosphor
Levensduur lichtbron	Up to 20,000
Lichtuitvoer	Up to 12,500 ANSI Lumens Dimable to 4,000 lumens
	NOTE: Up to 9,350 ANSI Lumens @ 110v
CLU (constante lichtuitvoer)	Yes
Contrastverhouding	20,000:1 (with DynaBlack enabled) 2,000:1 Sequential 600:1 ANSI
Helderheidsuniformiteit	>90%
Lensbereik	(R9801661) -TLD+ (0.41:1) -90 Degree Lens (R9862001) -TLD+ (0.73 - 0.94:1) -90 Degree Lens (R9801414) -TLD+ (0.92 - 1.33:1) (R9862005) -TLD+ (1.24 - 1.56:1) (R9862010) -TLD+ (1.49 - 2.02:1) * (R9862020) -TLD+ (2.01 - 2.76:1) * (R9862030) -TLD+ (2.69 - 4.41:1) * (R9862040) -TLD+ (4.37 - 7.35:1) * (R9829997) -TLD+ (6.95 - 10.83:1) * Standard Lens Option(s)
Optische lensverstelling	Up to 73% vertical lens shift & up to 28% horizontal lens shift (depending on lens selection) Visit the Barco Residential Lens Calculator for further information Download Lens & Airflow Data Here
Optische dowser	Yes
Kleurcorrectie	P7 RealColor™
Kleurenspectrum	Up to DCI (P3)
Beeldverwerking	Embedded Warp & Blend Engine
WARP	4-Corner Warp & Bow Correction via Warp Engine
Oriëntatie	360° Rotation
Netwerkverbinding	10/100 Ethernet via RJ45 connection
Geïntegreerde webserver	Yes
Diagnose	via Prospector web interface
HDR	HDR10
3D	Active Stereoscopic 3D Additional hardware required please contact an authorized Barco representative for details
Ingangen	1 x HDMI™ 2.0 (HDCP 2.2) 2 x HDBaseT (HDCP 1.4 -9Gbps only) 1 x Display Port 1.2 Quad 3G / 12G SDI / BarcoLink 1 x RJ45 Ethernet 1 x RS232 1 x USB 2 x DMX (1 x Input / 1 x Output) 1 x XLR for Wired Remote 2 x 3D Sync (1 x Input / 1 x Output) Optional Upgrade: Quad DP1.2
Invoeresoluties	HDMI™: Up to 4,096 x 2,160 @ 24/25/30/50/60Hz DisplayPort (Single Input): Up to 4,096 x 2,160 @ 24/30/50/60Hz via Optional Quad DP1.2 Input Card DisplayPort (Layout Mode: 2 x 2) *: Up to 1,920 x 1,080 @ 120Hz Up to 2,048 x 1,080 @ 120Hz DisplayPort (Layout Mode: 4 x 1) *: Up to 960 x 2,160 @ 120Hz * Specialist GFX cards may be required
Latentie	TBD
Controle	IR, RS232, IP, 12v Trigger Driver modules available for: Crestron, Control4, RTI & Savant WiFi (Optional), XLR Wired Remote, GSM (Optional)
Voedingsvereisten	110 -130V / 200 -240V / 50 -60Hz

Product specificaties**NJORD**

Energieverbruik	1,723 W Max
Geluidsniveau (standaard bij 25°C/77°F)	46 dB(A)
Bedrijfstemperatuur	0 to 40 °C at Sea Level Optimal Set Point: 20 °C
Operationele vochtigheid	0 to 80% (relative humidity)
BTU/uur	Max. 5,876 BTU/h @ 200 -240V Max. 4,811 BTU/h @ 110 -130V
Luchtstroomvereisten	Air Inlet (from Rear w/Feet Down): Front / Top / Right Exhaust (from Rear w/Feet Down): Rear Clearance Requirements: Front: 40cm Left: 1cm Right: 40cm Rear: 40cm Top: 40cm
Luchtuitstroom	152 ft ³ /min @ 25 °C 258 m ³ /hour @ 25 °C Download Lens & Airflow Data Here
Afmetingen (B x L x H)	Excluding Lens 540 x 725 x 355 mm 21.26 x 28.54 x 14 in.
Gewicht	Excluding Lens 48kg / 105lbs
Verzendingsafmetingen (L x B x H)	Including Pallet -Excluding Lens (Packaged Separately) 850 x 665 x 613 mm 33.46 x 26.18 x 24.13 in.
Verzendgewicht	TBD
Standaardaccessoires	Power Cord / Remote Control
Certificeringen	CE, FCC Class A and cCSAus
Veiligheidsvereisten	This projector may become Risk Group 3 (RG3) when an interchangeable lens with throw ratio greater than 2.3 is installed. Refer to the installation manual for further information.
Garantie	Limited 3 years parts and labor Extendable up to 5 years
*	Firmware upgradable Please contact an authorized Barco representative for details

Laatst bijgewerkt: 27 Mar 2024

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.