

RLM G5i Performer

With its compact design and sealed optics, the RLM G5i Performer is an ideal all-round projector suitable to both the rental as well as staging markets.



기술 사양

RLM G5I PERFORMER

일반 사양

광 출력	4500 ANSI Lumen
해상도	1024 x 768 (native)
명암비율	1000 : 1 (full field)
고명암비 모드	Available with special lenses
밝기 균일도	> 90%
램프	2 x 250 W mercury max. lifetime: 1500 hrs typ. lifetime: 1000 hrs min. lifetime: 750 hrs
소음도(@ 20°C -68°F)	42 dBA
소음도(@ 40°C -104°F)	46,5 dBA
주위 온도	Max 40°C (104°F)
전력 소비	700 W
기본 전압	92-240 V
무게	Projector: 25 kg (56 lbs) Frame: 5 kg (11 lbs)
크기(WxLxH)	705 x 707,8 x 316,5 mm
라이트 셔터	Standard
실드 DLP™ 코어	Standard
ScenergiX	Standard horizontal and vertical electronic edge blending
무이음경계선(Seamless) 전환	Standard (wipes, fades, ...)
PIP(Picture-in-picture)	Up to 4 sources simultaneously (2 data, 1 video and 1 SDI)
디지털 줌	Standard
렌즈 인코더	On zoom and focus (with TLD lenses)
연결 CLO(Constant Light Output)	not available
입력 소스 호환	1600 x 1200 (max. input)
고정 입력	<ul style="list-style-type: none">1x configurable 5 cable (BNC)1x composite Video (BNC)1x S-Video (4-pin DIN)1x analogue RGB (D15 Connector)1x SDI (+ loop through)1x DVI (Digital Visual Interface)
모듈형 입력	not available
컨트롤	<ul style="list-style-type: none">1 x RS-232 / 422 IN1 x XLR female (2 way)build-in RF remote transceiver (optional)
주문 정보	Projector Body: R9010320 Spare Dual Lamp:R9852940

작성일: 09 Jul 2024

© 2024 Barco nv. All rights reserved. 서면 허가 없이 전체 또는 부분을 복제하는 것은 금지됩니다. 모든 브랜드명 및 제품명은 상표, 등록 상표 또는 해당 소유자의 상표입니다. 지속적인 혁신으로 인해 정보 및 기술 사양은 사전 고지 없이 변경될 수 있습니다. 최신 사양은 www.barco.com을(를) 확인하세요.