


ImagePRO-4K

Scale, convert and switch images for the way shows are created in a 4K world



- The highest resolutions (4K 60p)
- The best color performance (4:4:4 sampling, 10-bit colors).
- The lowest latency for a scaler of this class (1 frame, progressive)

Superb performance

ImagePRO revolutionized live events in 2004. ImagePRO-4K goes even further as it easily scales, converts and switches the highest quality signals without latency (4K, 4:4:4, 60p, 10-bit), effectively solving glitches before they even occur.

The latest I/O connectors enable you to seamlessly convert HDMI 2.0, DP 1.2 and 3G-12G SDI signals while also enabling output image rotation.

Put simply, the flexibility and power of the ImagePRO is the backbone on which you build shows that run without a hitch.

Road-ready and reliable

Like all Barco image processing products, the ImagePRO-4K is built for life on the road. Assembled and tested for extreme use and abuse, the ImagePRO performs just as well at the gig as it does in the shop. What's more, the live-source view on the front panel provides you with a clear view of the incoming signal giving you the confidence you need to execute your event flawlessly.

LED at your fingertips

Need to slice and dice LED signals? The ImagePRO-4K does it with ease. Either chop up single inputs across several connectors, or drive multiple walls from multiple sources. The LED set-up menu will guide you through the process to achieve pixel perfect images. The 12-bit internal processing handles pre-scaling or cropping to an LED wall's actual resolution - in perfect detail.

Product specificaties**IMAGEPRO-4K**

General specifications	
Live-effectencanvas	N/A
Video-ingang	Comes loaded from the factory with a Tri-Combo input card supports <ul style="list-style-type: none">1x HDMI 2.0 4K60p 4:4:4 8bit, 4:2:2 10 bit,1x DisplayPort 1.2 4K60p 4:4:4 10bit,and 2x 12G SDI 4K60p 4:2:2 10bit or 4x 3G SDI 1200p@60p 4:2:2 10bit.
Video-uitgang	Comes loaded from the factory with a Tri-Combo output Card supports <ul style="list-style-type: none">1x HDMI 2.0 4K60p 4:4:4 8bit, 4:2:2 10 bit,1x DisplayPort 1.2 4K60p 4:4:4 10bit,and 2x 12G SDI 4K60p 4:2:2 10bit or 4x 3G SDI 1200p@60p 4:2:2 10 bit.
Genlock	Analog reference input on BNC connector. Blackburst and Bi-level at SD, and Tri-level at HD Reference output is provided by an internal sync generator capable of Bi-level and Tri-level sync signals
Aux-uitgangen met schaalverdeling	Up to 6x HD single scaler outputs or 2x 4K60p single scaler outputs supporting independent scaling, sizing, and color correction.
Mixers	N/A
Geheugenruimte voor foto's	Up to 100 HD or 25 UHD. Import file is size dependent.
Laageffecten	N/A
Multiviewer	Video preview on front panel
Uitbreidbaarheid	Future support for 2nd generation Event Master input and output cards (limited functionality on non-Tri-combo cards).
HDCP	HDCP compliance determined by installed cards.
Controle	<ul style="list-style-type: none">front panel menu and mappable buttonsEvent Master screen management software for PC or MACEvent Master controllers,WebUI,Ethernet RJ-45, 1000/100/10 Mbps autosense
Onderhoudsgemak	Field-Serviceable I/O cards (not hot-swappable)
Geluidsniveau	Estimated 37 dBA Nominal / 45 dBA Max Fan speed is software-managed based on operating temperature. Reference ISO 7779
Afmetingen	<ul style="list-style-type: none">Height: 4.37 cm / 1.72" 1 RU Rack mountWidth: 48.41 cm / 19.06" Incl. rack mountDepth: 40.41 cm / 15.91"
Gewicht	6.8 kg / 15.2 lbs
Vermogen	Input power: 100-240 VAC 50/60Hz 125w
Omgevingstemperatuur	0-40 C (32-104 F)
Omgevingsvochtigheid	0-95% non-condensing (non-operating) 0-85% non-condensing (operational)
Garantie	3 years parts and labor

Laatst bijgewerkt: 22 Jun 2023

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.