

iQ Pro R210L

Barco's Network Centric LCD projector with SXGA+ resolution and a brightness level of 2,200 ANSI lumens.



技术规格**IQ PRO R210L**

一般规格	
光输出	2,200 ANSI lumen
亮度均匀性	>95% for the total screen
对比度	> 800:1 (full white/full black)
液晶面板	3 active matrix 1.4" diagonal SXGA+ polysilicon LCD panels with Micro Lens Arrays and a resolution of 1400 x 1050 pixels (aspect ratio 4:3).
分辨率	1400 x 1050 (native)
网络	iQ Pro Server Specifications: -Processing Power: Pentium III socket with 1,2 Gigahertz Tualatin Celeron processor -Memory: 256 MB RAM -Storage: 40 GB hard disk -Video memory up to 64 MB -Inputs and outputs <ul style="list-style-type: none">▪ PCMCIA slot for Wireless LAN cards, memory cards, Bluetooth, input extensions ...▪ RJ45 connector for Ethernet (10Mb/s) and Fast Ethernet (100Mb/s)▪ 4 USB connectors▪ Audio: 3,5 mm jacks for Microphone in, Line in and Line out
特性	· Advanced picture-in-picture · Seamless switching with effects · Standard cable basket · Standard light shutter · Advanced digital zoom
兼容性	The iQ Pro R210L is compatible with: <ul style="list-style-type: none">▪ All current video sources (PAL,SECAM, NTSC) in Composite, S-VHS, Component or RGB formats▪ All currently proposed HDTV, extended and improved television standards (1080i, 720p)▪ All computer graphics formats from VGA, SVGA, XGA, SXGA to UXGA▪ Most Macintosh computers▪ Electronic workstations with a resolution up to 1600 x 1200 pixels at 75 Hz▪ Most computer sources with a pixel clock up to 160 MHz DVI sources up to SXGA
屏幕尺寸	From 1-6m/3-20 ft.
输入	· 1x Configurable 5-Wire (BNC) for: Composite Video, S-Video, Component Video , RGBHV, RGBS, RGsB. · 1 x Composite Video (BNC) (up to 7 Composite Video' s when using all connectors on top input board) · 1x S-Video (4-pin mini-DIN) (up to 3 S-Video' s when combining BNC' s) · 1x VGA (D15 connector) · 1x DVI (Digital Visual Interface)

技术规格**IQ PRO R210L**

灯泡	2x 120 Watt UHP lamp, in lamp housing Typical lifetime: 6000 h/lamp. 6000 hours in Dual Lamp Mode or max. 12000 hours/set in Single Lamp Mode
镜头	Fixed focal length lenses are available with a throw ratio of 0.85:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 7.0:1 (long throw). Variable focus lenses with a throw distance of 1.3-1.8,1.9-2.6, 3.0-6.0 times the screen width
扫描频率	Horizontal 15 kHz -110 kHz Vertical 25 Hz -150 Hz
镜头移动	V shift: -30% +110%
尺寸(宽x长x高)	Projector body with cable basket: 415 mm (Max W) x 195 mm (Max H) x 565 mm Projector body without cable basket: 415 mm (Max W) x 195 mm (Max H) x 487 mm (Max D)
净重	Net weight, body only: 12.9kg/28.5 lbs.
通信	<ul style="list-style-type: none">· 1x D9 connectors for RS232 In/Out· 1x spherical IR receiver
噪音级别	
电源	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
功率消耗	Max 380 Watt
功率消耗	Max 1297 BTU/h
安全级别	Compliant with UL1950 and EN60950
电磁干扰	BARCO's iQ Pro R210L complies with FCC rules & regulations, part 15 Class B and CE EN55022 Class B
无缝切换	standard

生成于: 16 Mar 2023

技术规格随时变化, 不会事先通知。请访问www.barco.com.cn, 获取更新信息。