

D-Cine Premiere DP90

2k Digital Cinema projector for screens up to 15m (49ft)



Product specificaties**D-CINE PREMIERE DP90****General specifications**

Lichtuitvoer	12,000 cinema lumens
Digital MicroMirror Device™	3 x 12" dark metal type Advanced DLP Cinema™ signal processing: CineCanvas™ image management; CinePalette™ color management, CineBlack™ contrast management and CineLink™ security management
Native resolutie	2048 x 1080
Behuizing	Hermetically sealed DMD™ and optical assembly
Schermbreedte	Screen width (screen gain 1.8) @ 14ftL: 17m -55ft adjustable light output CLO software
Montage	Standing or ceiling mounted Up to 7 degrees tilt via projection head
Lamp	1.5k to 4.0k Xenon arc lamp sizes Compatible with standard and high performance lamp types
Contrastverhouding	2000:1
Digitale video-ingangen	2 x SMPTE 292M inputsE 2 x DVI input both selectable as single or as dual link
Primelenzen	M25 1.25 -1.45:1 / M25 1.45 -1.8:1 / M25 1.8 -2.2:1 / M25 2.2 -3.0:1 zoom and M25 3.0 -4.3:1
Projectordiagnose	Via touch screen Via D-Cine Communicator control software (theater edition delivered standard on every product) Via SNMP agent
Voedingsvereisten	1 x 220V max. 17,000 BTU/hr (with 4kW lamp)
Afmetingen	projector: 640(H) x 730(W) x 1186.1(D) mm / 24.2(H) x 28.7(W) x 46.7(D) inch powerbox: 295.3(H) x 329.5(W) x 473.7(D) mm / 14.6(H) x 13.0(W) x 18.6(D) inch
Gewicht	projector: approx. 125kg (275lb) powerbox: approx. 20kg (44lb)
Opties	- CLO -Constant Light Output control - Anamorphic lens fitting for 1.25:1 scope lens - Acsar 2 Alternative Content Input Processor - ImagePRO HD - SNMP agent (v3)
Bestelgegevens	R9004440

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.