

iQ R400



Product specificaties

IQ R400

General specifications

Lichtuitvoer	4000 ANSI lumens
Helderheidsuniformiteit	>95 % for the total screen
Lcd-panelen	3 active matrix 1.3" diagonal XGA polysilicon LCD panels with Micro Lens Arrays and a resolution of 1366 x 1024 pixels (aspect ratio 4:3). LCD panels are selected for a minimum of pixel defects.
Resolutie	1366 x 1024 (native)
Netwerk	iQ Pro Server Specifications: -Processing Power: Pentium III socket with 1,2 Gigahertz Tualatin Celeron processor - Memory: 256 MB RAM -Storage: 40 GB hard disk -Video memory up to 64 MB -Inputs and outputs ■ PCMCIA slot for Wireless LAN cards, memory cards, Bluetooth, input extensions ... ■ RJ45 connector for Ethernet (10Mb/s) and Fast Ethernet (100Mb/s) ■ 4 USB connectors ■ Audio: 3,5 mm jacks for Microphone in, Line in and Line out
Lamp	2x 250 Watt UHP lamp, in lamp housing, pre-aligned for max. light output. Typical lifetime: 1000h/lamp. 1000 hours in Dual Lamp Mode or max. 2000 hours/set in Single Lamp Mode.
Beschikbare lenzen	- Fixed focal length lenses are available with a throw ratio of 0.85:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 7.0:1 (Long throw). - Variable focus lenses with a throw distance of 1.3-1.8, 1.9-2.6, 3.0-6.0 times the screen width.
Aanbevolen schermbreedte	From 1-6 m/3-20 ft.
Contrastverhouding	>400 : 1 (full white/full black)
Scanfrequenties	Horizontal 15 kHz -110 kHz Vertical 25 Hz -150 Hz
Kenmerken	- Standard cable basket · Standard light shutter · Advanced digital zoom · Advanced picture-in-picture · Seamless switching with effects
Compatibiliteit	-All video sources (PAL, SECAM, NTSC 3.58, NTSC 4.43) in composite, s-VHS, component -All currently proposed HDTV extended and improved television standards (1080i, 720p...) -All computer graphics formats from VGA, S-VGA, XGA, S-XGA to U-XGA -Most Macintosh computers -Electronic Workstations with a resolution of up to 1600x1200 at 75Hz -Most sources with a pixel clock up to 160MHz -DVI sources up to SXGA
Communicatie	1x D9 connectors for RS232 In/Out 1x spherical IR receiver
Ingangen	1x Configurable 5-Wire (BNC) for: Composite Video, S-Video, Component Video, RGBHV, RGBS, RGsB. 1x Composite Video (BNC) (up to 7 Composite Video's when using all connectors on top input board) 1x S-Video (4-pin mini-DIN) (up to 3 S-Video's when combining BNC's) 1x VGA (D15 connector) 1x DVI (Digital Visual Interface)
Wisselstroom	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
Geluidsniveau	
Energieverbruik	Max 620 Watt
Vermogensdissipatie	
Gewicht	Net weight: Body only 12.9 kg/ 28.5 lbs

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.