

OLite 612

12mm pixel pitch, 6,000 nits surface-mounted LED tile



12mm
PIXEL PITCH

IP65
WATERPROOF



Product specificaties**OLITE 612****General specifications**

| | |
|------------------------------|---|
| Pixelpitch | 12.4 mm |
| Helderheid | 6,000 nits |
| Led-configuratie | 3-in-1 SMD |
| Pixeldichtheid | 3,888 LEDs per tile (72x54) (rental) 1,944 LEDs tile (36x54) (fixed) |
| Pixeldichtheid | 3,888 LEDs per tile (72x54) (rental) 1,944 LEDs tile (36x54) (fixed) |
| Hor. kijkhoek | 110° (min 50% brightness) |
| Vert. kijkhoek | +40, -50° (min 50% brightness) |
| Contrastverhouding | 1,150:1 (at 500 lux) |
| Levensduur | 50,000 hours to 50% of initial brightness |
| Energieverbruik | 800W/tile (max) -240W average (rental) 400W/tile (max) -120W average (fixed) |
| Netspanning bij gebruik | 200-240V / 50-60Hz |
| Paneelafmetingen | Width: 896mm (rental) Height: 672mm (rental) Depth: 246mm (rental) Width: 448mm (fixed) Height: 672mm (fixed) Depth: 116mm (fixed) |
| Paneelafmetingen | Width: 896mm (rental) Height: 672mm (rental) Depth: 246mm (rental) Width: 448mm (fixed) Height: 672mm (fixed) Depth: 116mm (fixed) |
| Paneelafmetingen | Width: 896mm (rental) Height: 672mm (rental) Depth: 246mm (rental) Width: 448mm (fixed) Height: 672mm (fixed) Depth: 116mm (fixed) |
| Paneelafmetingen | Width: 896mm (rental) Height: 672mm (rental) Depth: 246mm (rental) Width: 448mm (fixed) Height: 672mm (fixed) Depth: 116mm (fixed) |
| Gewicht / tegel | 58 kg (rental) 17 kg (fixed) |
| IP-classificatie | IP65/65 |
| Verwerking | 16 bit/color |
| Kleuren | 281 trillion |
| Vernieuwingssnelheid | 800Hz |
| Opbouw voet | Max. 12 tiles high |
| Opbouw truss | Max. 15 tiles high |
| Link-interface | DVI interface (DVI connector) |
| Max. lengte link | 4.5m (with Barco DVI cable) |
| Interfaces | 2x DVI link |
| Max. stroomcascadeschakeling | 3 tiles |
| Onderhoudsgemak | Back |
| Bedrijfstemperatuur | -20 -45°C |
| Opslagtemperatuur | -20 -60°C |
| Operationele vochtigheid | 10-99% |
| Vochtigheid bij opslag | 10-99% |
| Broncompatibiliteit | CVBS, YC, YUV, RGB, DVI, SDI, HDSDI (DX700: and Dual link DVI, Dual link HDSDI) |
| Bedienbare digitizer | DX-700 (with DVI output card), D320, LED-PRO |
| Certificeringen | UL, CE class A, TUV, FCC, ClassA |

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.