


Atlas

Compact mechanical system designed to house Poly-Silicon LCD projection systems with XGA or SXGA resolution and different screen types in 67" or 84" diagonal.



技術仕様

ATLAS

一般仕様	
電源	95-230 VAC ± 10%, 50-60 Hz
輝度均一性	> 95 %
互換性	Barco's Atlas integrates with the existing network environment and video sources via BARCO's graphical control units: EOS Compact, Power and Ultra, Hydra and Visu+.
コントラスト	250:1
寸法ストラクチャ	Atlas 67" -XGA • Width 1368 mm / 53.86 in. • Height 1026 mm / 40.39 in. • Footprint 753 mm / 29.65 in. • Depth 897 mm / 35.32 in. • Socket height (min) 614 mm / 24.17 in. • Socket height (max) 1288 mm / 50.7 in. • Weight 108 kg / 238 lbs Atlas 67" -SXGA • Width 1335 mm / 52.56 in. • Height 1068 mm / 42.05 in. • Footprint 798 mm / 31.4 in. • Depth 942 mm / 37.1 in. • Socket height (min) 492 mm / 19.4 in. • Socket height (max) 1288 mm / 50.7 in • Weight 108 kg / 239 lbs Atlas 84" -XGA • Width 1708 mm / 67.24 in. • Height 1281 mm / 50.43 in. • Footprint 1041 mm / 41 in. • Depth 1186 mm / 46.68 in. • Socket height (min) 486 mm / 19.13 in. • Socket height (max) 1288 mm / 50.7 in • Weight 138 kg / 305 lbs Atlas 84" -SXGA • Width 1650 mm / 65 in. • Height 1320 mm / 52 in. • Footprint 1079 mm / 42.5 in. • Depth 1225 mm / 48.2 in. • Socket height (min) 366 mm / 14.4 in. • Socket height (max) 1288 mm / 50.7 in • Weight 138 kg / 305 lbs
環境準拠	• Operating temperature: 17 °C -27 °C or 62 °F -80 °F • Humidity: recommended 40% -60%, non condensing Typical for stitched screens. Consult download for more info on screen modules.
ランプ	100 Watt lamp Operation time 8,000 hours (average)
LCD パネル	• XGA with 3-panel Poly-Silicon LCD, 4:3 • SXGA with 3-panel Poly-Silicon LCD, 5:4
輝度	Atlas 67" XGA -130 cd/m² 38 ftL Atlas 67" SXGA -110 cd/m² 32 ftL Atlas 84" XGA - 262 cd/m² 77 ftL Atlas 84" SXGA -220 cd/m² 65 ftL
輝度流動	XGA -500 lumens SXGA -600 lumens
オプション	All projector settings are accessible through Barco's wall management software. Full features of this software can be viewed under this website 'Application software'
消費電力	XGA resolution -140 W SXGA resolution -220 W
解像度	XGA -1024x768 pixels SXGA -1280x1024 pixels depending on the projector, screen type and size used
対応スクリーンサイズ	• 67" or 84" diagonally • High gain screens for high brightness and high contrast black screens for wide viewing angles • Other screens on request • Download the brochure for more info on the principles and technologies

生成日:09 Jul 2024

© 2024 Barco nv.(C) Barco. All rights reserved. (無断転載を禁ず。) 書面による許可なく全部または一部を複製することは禁止されています。すべてのブランド名および製品名は、それぞれの所有者の商標、登録商標、または商号です。継続的な技術革新により、情報および技術仕様は予告なく変更される場合があります。最新の仕様についてはwww.barco.comをご確認ください。

