

AC-AR03

A-frame arm



The AC-AR03 arm is designed for installation at waist height in a typical hospital bedside application. The arm can be fixed to a wallbox and can be easily parked away from the bedside when necessary.

A perfect fit for bedside terminals

The arm is easily manoevrable to provide the user with the optimum position when using the touchscreen interface. The "A frame" arm integrates a custom gas spring and movement mechanism which is adjusted especially to fit with the Smart Terminal attached to the arm.

Product specifications**AC-AR03****General specifications**

Color	Barco White
Articulation forces allowed	< 30 N
Reach	Overall reach of 1500 mm
Height	Height adjustable +70° to -30°
Cover	Fully covered for ease of cleaning
Cable management	All cabling is internal to the arm
VESA	Custom VESA attachments 75mm
Movement	Ease of movement in all articulations
Carrying capacity	1.0 -7.0 kg (pre-configured per terminal)
Arm weight	6.5 kg including heat sink, 6.3 kg without heat sink

Last updated: 08 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.