

RetroData 808s + Iris³



Product specifications**RETRODATA 808S + IRIS³**

General specifications

Compatibility	Horizontal autolock scan frequency of 15-75 kHz Vertical autolock scan frequency of 37-200 Hz RGB bandwidth of 75 MHz A wide range of PC graphics boards with a resolution up to 1280 x 1024 pixels/70 Hz Universal connection possibilities
Light output	364 ftL. (at 10 % peak white) 41 ftL. (Economy mode) 57 ftL. (Normal mode) 62 ftL. (Boost mode)
Screen size	67"

Last updated: 08 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.