

ClickShare CSE-200

Wireless presentation system for small to medium sized meeting rooms



- **Wireless connection to central screen**
- **Up to 2 users on-screen**
- **Share from laptop, tablet or smartphone**
- **Enhanced security features**
- **Touch back support**
- **Central management**
- **Delivered with 2 Buttons**

Creativity is one of the core assets of your organization. With ClickShare, you can make sure ideas receive the attention they deserve. This wireless presentation system allows users to simply share what's on their laptop or mobile device, on the presentation screen. No cables, no set-up, no waiting to join in.

Find out what's new in the latest ClickShare update

Plug in to stand out

The CSE-200 offers the ClickShare experience for small and medium-sized meeting rooms. Anyone – including guests – can connect with one click and share right away, without the need for any training. Users simply plug a USB-powered device – the ClickShare Button – into their PC or Mac and click the button to get the content from their laptop on the large meeting room screen. With the ClickShare Apps, users can also share content from their laptops, mobile phones or tablets. Make sure to have the latest firmware installed on your Base Unit to enable the best experience with the Desktop App.

Encouraging collaboration

The CSE-200 was designed for enterprise rollouts and offers enhanced security features, a wider range of connectivity options – including AirPlay and Google Cast support for non-HDCP content – Touch back function and central management. Allowing up to 2 persons to share content simultaneously, the CSE-200 ensures direct connectivity to the central screen and encourages collaboration. For user convenience, security features of the CSE-200 can be set to one of three predefined levels, depending on the company's policies and needs. Last but not least, the device's API also makes integration into the company network a lot easier. ClickShare also enables the touch back function in your meeting rooms. Run any application from your laptop and control it

The CSE-200 was designed for enterprise rollouts and offers enhanced security features, a wider range of connectivity options – including AirPlay and Google Cast support for non-HDCP content – Touch back function and central management. Allowing up to 2 persons to share content simultaneously, the CSE-200 ensures direct connectivity to the central screen and encourages collaboration. For user convenience, security features of the CSE-200 can be set to one of three predefined levels, depending on the company's policies and needs. Last but not least, the device's API also makes integration into the company network a lot easier. ClickShare also enables the touch back function in your meeting rooms. Run any application from your laptop and control it from the screen. With a few touches on the screen, open presentations, share mails, start a video. Focus on audience and content instead of on your presentation tool.

The CSE-200 is a product created with ISO 27001 certified flows and processes.

Adding ClickShare CSE-200 to your fixed conference room set-up (like a Microsoft Teams or Zoom room) enhances productivity and collaboration in your Microsoft Teams and Zoom meetings. It brings the focus from conferencing back to truly collaborating.

Product specifications

CLICKSHARE CSE-200

General specifications

Operating system	Windows 10 32 & 64 bit macOS 10.14/10.15 (Catalina) Android 9 & 10 (ClickShare app) iOS 11, 12 & 13 (ClickShare app)
Video outputs	1x HDMI 1.2
Output resolution	1920x1080 @60Hz
Audio	Via HDMI, analog via Audio Jack 3.5mm, S/PDIF
AirPlay Support	iOS 11, 12 & 13 / macOS 10.14, 10.15
Google Cast Support	Android 9, 10
Frame rate	Up to 30fps*
Number of sources simultaneous on screen	2
Number of simultaneous connections	16
iPad, iPhone and Android compatibility	Sharing of documents, browser, camera for both Android and iOS devices via ClickShare app or using AirPlay / Google Cast
Extended desktop	Available for Windows, requires ClickShare Extension Pack.
Authentication protocol	WPA2-PSK in stand-alone mode WPA2-PSK or IEEE 802.1X using the ClickShare Button in network integration mode
Wireless transmission protocol	IEEE 802.11 a/g/n
Reach	Adjustable with signal strength modulation; max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit
Frequency band	2.4 GHz and 5 GHz (DFS channels not supported)
Connections	1x Ethernet LAN 100Mbit 2x (back) + 1x (front) USB Audio analog line out on mini jack socket (3.5mm), digital S/PDIF
Noise Level	Fanless
Temperature range	Operating: 0°C to +40°C (+32°F to +104°F) Max: 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	Kensington lock
Certifications	FCC/CE
Warranty	3 years standard Possible to extend to 5 years
*Note	*In optimal WiFi conditions with minimal WiFi interference and as measured during our quality validation. Check Network Deployment Guide for more info on WiFi optimisation and ideal configuration depending on your network environment.

ClickShare Base Unit dimensions

Dimensions (HxWxD)	205mm x 115mm x 45mm (excl. antennas) / 8.1" x 4.5" x 1.8" 205mm x 150mm x 135mm (incl. antennas) / 8.1" x 5.9" x 5.3"
Power supply	Standard 110/220 V AC plug or Power over Ethernet (PoE Plus)
Power consumption	Operation: 6W (typical) / 18W (max) Standby: 2.6W (ECO standby) / 0.4W (Deep standby)
Weight	600g / 1.32lbs

Last updated: 04 Dec 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.