

CLM-HD6

6,000 lumens, 1080p HD, single-chip DLP projector



Barco's CLM-HD6 projector is designed on an efficient hardware platform. It offers a 6,000 lumens light output, full HD resolution and advanced input options at a highly competitive price. It is primarily designed for meeting rooms, medium-sized auditoriums, lobbies and museums.

Improved colors

The CLM-HD6 is a single-chip DLP projector with advanced color saturation and a full HD resolution. The projector's resolution and 6,000 lumens light output are ideal for single-screen applications that require a clear image and need to feature modern, high-definition images and video without quality loss.

Bright, silent and reliable

The CLM-HD6 is an attractive option for customers that want to project in bright HD and need the best quality guarantee at the most comfortable price. Due to its power-saving options, redundant lamp system and durable, proven technology, the CLM also offers a low total cost of ownership. If you want a reliable, bright and silent unit that does the job, the CLM-HD6 was designed for you.

Product specificaties**CLM-HD6****General specifications**

Type projector	Full HD single-chip DLP projector
Technologie	0.65" DMD™ x1 color wheel: RGBYW
Resolutie	1,920 x 1,080
Helderheid	6,000 center lumens / 5,700 ANSI lumens
Contrastverhouding	>1,300:1
Helderheidsuniformiteit	95%
Beeldverhouding	16:9
ScenergiX	N/A
Type lens	CWH
Lensbereik	0.81:1 ; 1.27-1.52 ; 1.52-2.03 ; 2.03-3.85 ; 3.85-7.32
Optische lensverschuiving	Vertical: -20% -+120% / Horizontal: 20% (L) to 20% (R) on zoom lenses
Kleurcorrectie	P7
Lampen	2x330W
Levensduur lamp (standaard)	1,500 hrs / 2,000 hrs (max)
Transport met lamp	Yes
Lampbehuizing, snelle vervanging	Yes, auto lamp select
Lampvervanging door klant	N/A
Lampgarantie	120 days or 500 hrs
Verzegelde DLP™-kern	Yes
Optische dowser	N/A
Geavanceerde Picture-in-Picture	Up to two sources simultaneously
Oriëntatie	table -ceiling -vertical -side (portrait)
DMX 512	N/A
WARP	H+V keystone, pincushion
Geïntegreerde webserver	N/A
CLU (constante lichtuitvoer)	Optional
3D	N/A
Ingangen	2 x HDMI (HDCP 1.3); 5-BNC (RGBHV, RGBS/RGBsB;YUV); VGA (RGBHV, RGBS/RGBsB;YUV); cinch (RGBs, YUV) Composite video; S-Video
Optionele ingangen	N/A
Invoerresoluties	From NTSC up to UXGA (1600 x 1200), incl. HDTV (1920 X 1080)
Max. pixelklok	165 MHz
Softwaretools	Projection Toolset
Controle	IR, RS232, 12v out
Netwerkverbinding	10/100 Base-T, RJ-45 connection
Voedingsvereisten	100 -240V / 50 -60 Hz
Energieverbruik	905W / Standby mode:
Geluidsniveau (standaard bij 25°C/77°F)	40dB(A)
Operationele omgevingstemperatuur	0°-40°C / 32°-104°F
Vochtigheid in bedrijf	0-80% (non-condensing)
Dissipatie BTU	max. 3,087 BTU/h
Afmetingen (B x L x H)	436 x 550 x 236mm / 17.16 x 21.65 x 9.29 inch
Gewicht	24kg (53 lbs)
Verzendingsafmetingen	(WxLxH) 661 x 822 x 380mm / 26.02 x 32.36 x 14.96 inch
Standaardaccessoires	Power cord; wireless remote control, HDMI to DVI adaptor
Verzendgewicht af fabriek	27kg (59.5lbs)
Certificeringen	Complies with FCC rules & regulations, part 15 Class A and CE EN55022 Class A, RHoS
Garantie	3 years standard, 4th or 5th year optional

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.