

ScreenSHAPER

ScreenSHAPER Video Mapping System corrects distortion created when an image is projected off-axis or on a surface that is not flat. ScreenSHAPER can also perform image rotation, image mirroring and scan conversion.



Технические характеристики

SCREENSHAPER

Общие характеристики	
Ввод видео	Number: 1 Video Signal Format: Accepts analog (RGB) and digital (DVI) video Resolution: Supports resolutions up to 1280x1024, 60 Hz, non-interlaced Input Sync Format: Separate H & V Sync, C sync or Sync on Green Connector: DVI-I connector supports both digital and analog input; HD-15 adapters are available. Termination: 75 ohms for analog video
Вывод видео	Number: 1 Video Signal Format: Outputs analog (RGB) and digital (DVI) video Resolution: Supports resolutions up to 1280x1024, 60 Hz, non-interlaced Output Sync Format: Separate H & V Sync, C sync or Sync on Green. Connector: DVI-I connector supplies digital and analog output; HD-15 adapters are available. Output Impedance: 75 ohm for analog video
Видеообработка	Processes the entire input image or a user-defined "area of interest" in real time Transport delay: 2 frames User-selectable Output Format: VGA(640x480), SVGA(800x600), XGA(1024x768), SXGA(1280x1024) WARP MODE Geometry Correction: General-purpose algorithm supports precise alignment ROTATION MODE Supports independent X,Y scaling for aspect ratio correction. Supports rotation in 90-degree increments: 0, 90, 180 and 270 Image Flip: Left-to-right and top-to-bottom
Возможности управления для пользователя	Front Panel Controls: Electro-luminescent display, control knob and six keys provide a menu-based front panel interface to simplify set-up and adjustments. Remote Control: RS-232/RS-485 serial interface provides remote control of all functions.
Физический	Width: 17"(432mm) or 19"(483 mm) with rack mount option Height: 1.75"(44.5mm) one Rack Unit Depth: 16"(454.5mm) all input/output connectors are mounted on the rear of the unit Weight: 9 lbs (4.1 kg); Shipping Weight: 13 lbs (5.91 kg)
Входная мощность	98-264 VAC, 47-63 Hz, auto-ranging, 45 watts maximum
Относящийся к окружающей среде	Operating temperature: 0-40 degrees C Humidity: 0-95%, non-condensing
Гарантия	All video products are designed and tested to the highest quality standards and are backed by a full three-year parts and labor warranty.

Создано: 15 Mar 2023

Технические характеристики могут изменяться без предварительного уведомления. Для получения самой последней информации посетите веб-сайт www.barco.com.