

# FLDX 1.2 - 1.7 : 1 (EN63)

WUXGA 1.12-1.58:1 WQXGA/4K 1.20-1.70:1 F80: 1.59 - 2.24 : 1 (WQXGA/4K UHD) (F80 requires the FLD/FLD+ lens adapter)



**Product specifications****FLDX 1.2 - 1.7 : 1 (EN63)**

General specifications	
Platforms	For F35, FL40, F70, F80* and F90 projector series *requires lens adapter R98014421. F80 specific throw ratio: 1.59 -2.24 : 1 (WQXGA/4K UHD)
Working F/#	F 2.4-2.7 Motorized Iris F# 2.4-6.5 with memory
Zoom ratio	1.42 Motorized zoom and focus with memory
Focal length	23.95-34.02 mm
Focus Range	Standard: 1.5m – 15m
Weight	2.8 kg
Shipping weight	3.4 kg
Throw Ratio	DMD chip WUXGA 1.12-1.58 :1 WQXGA 1.20-1.70:1 Image size tolerance +/-2%

Last updated: 28 Aug 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.