

SLM G5 Executive



技术规格

SLM G5 EXECUTIVE

一般规格

光输出	5,000 ANSI 流明
数字微镜器件	three XGA DMDs (1024 x 768)
亮度均匀性	Brightness uniformity: >90% for the total screen
分辨率	1024 x 768 (本机)
对比度	> 500:1 (full white/full black)
特性	<ul style="list-style-type: none">■ 画中画■ 带效果的无缝来源切换
功率消耗	1600 Watt
兼容性	All video sources in Composite, S-VHS, Component or RGB formats or serial digital format All currently proposed HDTV, extended and improved television standards Most Macintosh computers Computers and electronic workstations with a resolution up to 1600 x 1200 pixels Two digital input slots allow direct digital interfacing with current and future digital inputs
尺寸(宽x长x高)	529 x 795 x 429 mm (20.8 x 31.3 x 16.9 inch)
灯泡	1.2 kW Xenon illumination system
镜头移动	TLD Lenses Motorized V shift: -20% +118% Motorized H shift: max. 65% (L+R) For specific details per lens type: see lens product pages
镜头	Fixed focal length lenses are available with a throw ratio of 0.8:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 1.2:1 (long throw). Motorized Zoom Lenses with a throw distance of 1.6-2.0,2.0-2.8,2.8-5.0,5.0-8.0 times the screen width
网络连接	Optional
ScenergiX	Optional
屏幕尺寸	5 -15米/ 6 -50英尺
封装DLP™内核	Optional
无缝切换	标准
净重	净重: 45千克/99磅

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。