

DP2K-10S

Small DLP Barco Alchemy Cinema projector (9,000 lumens)



- **Integrated, DCI-compliant**
- **Combines media server functionalities with Series 3 cinema processing electronics**

The DP2K-10S projector is a compact, fully integrated digital cinema projector designed for smaller theaters, boothless cinemas and single screens. By merging the projector and media server functionalities into one single projector module, the DP2K-10S Barco Alchemy projector is a full-fledged, DCI-compliant projector and media-server solution that includes on-board storage. Reducing the required hardware, it increases simplicity and reliability in the projection booth. And for additional reliability, the smart projector detects potential operational errors and warns users if, for instance, a scheduled show is missing assets or KDMs. Great in TMS environments, it operates stand-alone in single-screen applications. Thanks to the embedded Barco Web Commander user interface, shows can be created and scheduled remotely.

DCI image quality

Built upon Barco's renowned DP2K cinema projectors, the DP2K-10S guarantees crisp images over time thanks to its acclaimed manual color convergence mechanism. While its standard Xenon lamps offer vibrant colors, its motorized lenses ensure a perfect image ratio at all times.

Low cost of ownership

Geared with integrated technology that drives operational and maintenance costs down, the DP2K-10S offers DCI image quality and ultimate reliability at a low TCO. As such, it is the perfect choice for exhibitors looking for a worry-free solution to go digital with a minimal hassle and risk. The DP2K-10S projector is also available in a package with a third-party media server and it can be ordered without the Barco Alchemy module as well.

Unique benefits of Barco Alchemy technology



- Combines media server functionalities with cinema processing electronics
- Fewer boxes lead to more reliability and ease-of-use
- Simple operation thanks to intuitive 'Barco Web Commander' user interface
- Easy upgrading of Series 2 projectors with Barco Alchemy module
- Specifically designed for smaller theatres, independent cinemas, art houses, boothless cinemas and single screens
- Low cost of ownership thanks to integrated Barco Alchemy technology, included storage, stand by eco-mode, reusable air filters, and shared components with other Barco projectors.
- DCI image quality at all times thanks to the easy-to-use manual convergence mechanism
- Wide range of motorized lenses for a correct image ratio
- Maximum ease-of-use through intuitive Barco Web Commander Screen Management System, running via a web browser
- Barco Communicator for simple configuration and updates of all modules in the projector
- Consistent image quality and brightness thanks to the proprietary sealed engine and advanced DMD cooling
- Easy to transport, install and service thanks to its integrated handles, user-friendly software tools and smart modular architecture

Product specificaties

DP2K-10S

Preliminary technical specifications. These are subject to change without prior notice.

Digital MicroMirror Device™	3 x 0.69" DC2K dark metal devices
Native resolutie	2,048 x 1,080 pixels
Behuizing	Hermetically sealed DMDs and optical assembly
Lamp	2.2kW, short-arc Xenon
Lichtuitvoer	9,000 lumens
Schermafmaat	Up to 10m/33 ft wide (screen gain 1.2 @ 14ft)
Contrastverhouding	1,850:1
Primelenzen	Fully motorized 1.2 -1.7 1.34 -1.9 1.5 -2.15 1.7 -2.55 2.0 -3.9
I/O-controle	3x Ethernet (RJ 45) 8x GPIO (DB 25) 3D interface USB interface
Integrated Cinema Media Processor	DCI 4K 2D up to 60fps* DCI 4K 3D (24 or 30 fps per eye)* DCI High Frame Rates 2K 3D up to 120fps (60fps per eye) JPEG 2000 bit-rates up to 625Mbps Dual-channel color-correction MPEG-2 (4:2:0 and 4:2:2 up to 60fps) 2x Displayport 2x 3G-SDI inputs 1x HDMI 1.4a (up to 4K 2D 24fps, support for BluRay 3D) 16x AES/EBU audio channels (2x RJ45) 8x GPI, 8x GPO (4x RJ45) 2x Gbe for content connectivity & ingest 2x front-accessible USB 3.0 for fast ingest 2x front-accessible USB 2.0 Video watermarking: Civolution NexGuard Audio watermarking: Civolution Closed captioning devices: Support for SMPTE 430-10 * 4K 24fps is standard. For 4K 60 fps / 4K 3D on ICMP upgrade modules a license is required. Newly-built 4K Barco Alchemy projectors have the license standard included.
Geïntegreerde opslag	1.9TB effective storage (RAID-5) / 3x 1TB Hot-swappable 2.5" hard-drives 3.9TB effective storage (RAID-5) / 3x 2TB Hot-swappable 2.5" hard-drives
Barco Web Commander	Projector Dashboard Projector Control Board Show Player/Editor/Scheduler Automation, 3D, Ingest Dynamic DCP playlists & intermission TMS integration Smart Projector Status Via HTML5 web-browsers including iOS & Android tablets Dual projector 3D: passive and active Auro 11.1 decoding
Barco Communicator	Projector installation & configuration Projector update & maintenance
Voedingsvereisten	220 V
Projectorafmetingen (H x B x D)	325 x 626 x 925 mm 12.8 x 24.7 x 36.4 inch
Projectorgewicht	Recessed handles for easy carrying 56.5 kg / 125 lbs for carrying (lamp-house removed) (66.5 kg / 147 lbs total weight)
Omgevingstemperatuur	35°C / 95°F Max.
Luchtuitstroom	140 – 180 CFM (4 – 5 m ³ /min)
Veiligheidsvereisten	Class 1 risk group 3
Opties	3D add-ons Touch screen monitor, inc. Barco Commander & Communicator Pedestal CineCare Web Auro 11.1 license Barco Escape license Live 3D*** *** Software roadmap

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.