

OverView OSV-560F

Long lifetime seamless flat 6.2 megapixels collaboration video wall



The OverView OSV-560F is a high-performing video wall, ideal to visualize and evaluate huge amounts of information in 24/7 environments. Featuring a large, flat, panoramic seamless canvas, a mix of data and video can be displayed simultaneously in high quality without the interruption of a seam or a bezel.

Furthermore, by benefiting from proven rear-projection technology, state-of-the-art controllers and advanced signal processing, the OSV offers a feature-rich solution with high image quality and excellent reliability. Compact in setup, this video wall suits a multitude of possible applications from crisis operations and war rooms, to brainstorm and planning rooms, and of more traditional control room applications in utilities, energy and process control.

All the advantages of LED technology

Images are displayed on the OSV using Barco's LED-lit rear-projection technology, which has a long track record in the control rooms market. This means these seamless video walls benefit from the many advantages of LED technology, including: very low maintenance, substantially reduced power consumption, and long lifetime. The use of DLP projection technology makes the solution fit for 24/7 use, preventing the image retention (e.g. a burned-in company logo) often seen in less qualitative solutions. The OSV-560F consists of five blended rear-projection cubes, forming one seamless image.

A real seamless canvas

No matter how thin, seams and bezels are always a nuisance. Especially when displaying numbers or other critical content, any interruption is too much. OSV's Seamless canvas makes sure a wealth of different sources can be positioned anywhere on the screen, in the most efficient way.

Saving real estate space

Compared with conventional rear-projection systems, the OSV video walls have a limited depth of less than 1.2 meters/47 inches. In this way, the available real estate space is used to its maximum.

High brightness

The OSV HB series is equipped with laser-phosphor projection technology, strongly boosting its brightness levels. This allows the system to be used in environments with challenging lighting conditions.

Free from image retention

The OSV uses DLP technology, which is not sensitive to image retention. This means you can show static images without risking burn-in effects.

Enhanced immersive user participation

The use of a curved screen creates an immersive effect that makes everyone in the room feel more involved, which improves the collaboration.

More pixels

Compared with the OSV LL series, the OSV HB series has a 30% higher resolution. This means that even more information can be displayed on the seamless canvas.

Real-life collaboration

The large screen area, gives all participants in a telepresence meeting a front row seat. Using 3, 5 or 7 rear-projection modules, the horizontal size of the OSV system varies from 3.5 to 6.5 meters (120 to 240 inches).

Product specifications**OVERVIEW OSV-560F****General specifications**

Resolution	6.2 Mega Pixels
Pixel size	1 mm
Brightness	80 Nit (cd/m ²)
System contrast	25:1 with 100 lux ambient light on-screen
Color	Up to 165% EBU
Display technology	Rear projection DLP
White point	2,300K 6,500K 9,300K arbitrary
Brightness uniformity	90% ANSI 9
Color stability	Self calibrating with spectrometer based Sense6
Screen	Barco Semi-Rigid Seamless Rear Projection Screen
Screen gap	None. No seams or bezels
Screen size	4415 (length) x 1400 (height) mm 173.8 (length) x 55 (height) inch
Radius	N/A -flat screen
H / V half gain angle	60° both horizontal and vertical
Screen reflectivity	2%
Dimensions (physical)	5214 (length) x 2370 (height) mm 205 (length) x 93.3 (height) inch
Image start height	750 mm / 29.5 inch above floor
Depth	Center: 1170 mm / 46 inch
Weight	830 kg / 1830 lbs
Light source	6x redundancy for each of 3 LEDs
Light source lifetime	> 60,000 h > 80,000 h (eco)
Recommended maintenance interval	> 5 years No burn-in, no image retention
Conditions for operation	10°C-40°C, 50°F-104°F 80% humidity (non condensing)
AC input voltage	110 – 240 V, 50-60Hz
Power	Typical: 1780 W ; Maximum: 2450 W
Heat dissipation	Typical: 6079 BTU/h ; Maximum: 8367 BTU/h
Signal inputs	Twin dual link DVI-D
Input frequency	300 MHz
Integration to third party equipment	Web based API
Warranty	2 years

Last updated: 08 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.