

# ClickShare CX-M

CX-M is the ClickShare Module used with display. The CX-M is combined with the display to form a Wireless All-in-One Display. When the laptop is inserted into the button, the built-in microphone and camera of the All-in-



- **Wireless Bring Your Own Meeting (BYOM) functionality**
- **Seamless video meetings from your laptop using the Button or App**
- **Increased collaboration with 2 sources on screen**
- **Smart Meeting Flow for streamlined collaboration**
- **Plugging in the Button can wake up the base unit and display**
- **100% secure, encrypted and cloud-managed**

ClickShare CX-M enables wireless conferencing in medium-sized meeting spaces. When you walk into the meeting room, ClickShare automatically connects you to room devices like cameras, mics, speakers, sound bars and displays.

Start a meeting from your laptop within seconds, using your preferred video conferencing platform. Make hybrid meetings easy, with just one click on the ClickShare Button or the ClickShare App, both for employees and guests.

**Product specifications****CLICKSHARE CX-M****CX-M Specifications**

Video Outputs	4K UHD (3840*2160) @ 30Hz. HDMI 1.4b(OPS 80pins connector) or USB-C DisplayPort 1.2
Audio output	USB
USB	1 X USB-C
ClickShare Buttons	1
ClickShare App	Desktop & Mobile
Native protocols	Airplay, Google Cast, Miracast
Maximum sources simultaneously on screen	2
Noise Level	Max. 25dBA @ 0-30°C Max. 30dBA @ 30-50°C
Authentication protocol	WPA2-PSK in stand alone mode WPA2-PSK or IEEE 802.1X using the ClickShare Button in network integration mode
Wireless transmission protocol	IEEE 802.11 a/g/n/ac and IEEE 802.15.1
Reach	Max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit
Frequency band	2.4 GHz and 5 GHz
Connections	1x Ethernet LAN 1Gbit 1x USB-C 3.0 (front) 1x OPS-80 pin
Temperature range	Operating: 0°C to +40°C (+32°F to +104°F) Max: 40°C (104°F) at 5000m Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	NA
Certifications	SRRC/CE
Touch screen support & Interactivity	Yes
Local view	Yes
Wireless conferencing	via App or Button
Network connection	LAN & WiFi
Management and reporting	Yes
Warranty	1 year standard. 5 years coverage upon registering via SmartCare
Dimensions (HxWxD)	202mm x 119mm x 30mm
Power consumptions	Operational: 5-10W, 16W Max
Power Supply	18V DC from OPS display
Weight	698g

**Last updated: 29 May 2025**

© 2025 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.