

SP-4816

16mm pixel pitch, 6,000 nits LED sports perimeter system



High return on investment

With over 20 years of experience in outdoor, large-screen LED displays and visual solutions for the broadcast industry, Barco knows how to get the best image to your TV audience, and the highest return on your advertising investments. Our patented, top-mounted 'brand-up' display offers even additional visibility and a higher return for advertisers.

Superior image reproduction for broadcast

Barco's sports perimeter enables perfect, flicker-free reproduction of brands through its excellent daylight readability, superior contrast levels, easy synchronization with professional camera equipment, and individual color optimization. Barco's LED sports perimeter is designed for both fixed and mobile applications. 225 meters of the sports perimeter can be easily loaded on just one truck, and set up in less than three hours.

Product specificaties

SP-4816

General specifications

Pixelpitch	16mm
Helderheid	6,000 nits (typical)
Pixeldichtheid	11,250/sqm 1,046/sqf
Led-configuratie	1R, 1G, 1B
Hor. kijkhoek	+70° / +70° color shift
Vert. kijkhoek	-10° / +35° color shift
Energieverbruik	200 W/m ² (typical)
Warmtedissipatie	682 BTU/hr (typical)
Kleurverwerking	14-bit/color
Bedrijfstemperatuur	-10°C to 45°C (14°F to 113°F)
Operationele vochtigheid	10 to 99%
Gewicht / tegel	90kg (198.4lbs)
Afmetingen (B x L x H)	2,560 x 160 x 800mm (100.8 x 6.3 x 31.5 inch)
Onderhoudsgemak	Back
Robuustheid	IP65 (front) / IP54 (back)
Certificeringen	CE/ETL/RohS

Laatst bijgewerkt: 08 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

