

iCon H500

Network-centric, 1080p HD, 5,000 lumens, single-chip DLP projector



Product specificaties**ICON H500****General specifications**

Lichtuitvoer	5000 ANSI lumens
Resolutie	1920 x 1080 (native)
Helderheidsuniformiteit	> 95% for the total screen
Lamp	2x 250 Watt P-VIP lamp in lamp housing, pre-aligned for max. light output. Typical lifetime: 1,500 h/lamp
Optische uitrusting	Sealed optical engine
Contrastverhouding	> 2000:1 (full white/full black; depending on lens, focus and projector settings)
Beeldscherm	1-chip 0.95" DarkChip3@ DLP™ 1080p panel with BrilliantColor™ processing and a native HDTV resolution of 1920 x 1080 pixels, 16:9 aspect ratio
Kleurencirkel	RGBW
Kenmerken	<ul style="list-style-type: none">■ Advanced picture-in-picture (PiP)■ Intelligent dual lamp system■ On board PC with Windows OS for network centric operation■ Advanced desktop integration (source and PiP handling through Windows OS)■ Sealed optical engine■ Standard cable basket
Ingangen	<ul style="list-style-type: none">■ 1x Component video, RGBHV, RGBS or RGsB (5x BNC)■ 1x Composite video (BNC)■ 1x S-video (4-pin mini-DIN)■ 1x VGA (D15 connector)■ 2x DVI-D (Digital Visual Interface-Digital)
Uitgangen	<ul style="list-style-type: none">■ 1x DVI-D
Compatibiliteit	<ul style="list-style-type: none">■ All current video sources in composite, S-video, component or RGB formats■ All current HDTV sources (720p, 1080i)■ All computer graphics sources with a pixel clock up to 270 Mhz (VGA, S-VGA, XGA, SXGA, SXGA+, UXGA, QXGA: 2048x1536)■ DVI sources up to UXGA and HDTV resolution■ Apple Macintosh formats
Scanfrequenties	Horizontal 15kHz -140kHz Vertical 25Hz -150Hz
Communicatie	<ul style="list-style-type: none">■ 1x D9 connector for RS-232■ 1x IR remote receiver■ 4x USB■ 1x RJ45 ethernet■ 1x PCMCIA slot (Type II)
Schermformaat	From 1.2 -6m / 4 -20ft
Lensverschuiving	Max. vertical shift from -25% to +140% (with QCLD 0.85:1 lens: +/-25%)
Geïntegreerde beeldschermserver	<ul style="list-style-type: none">■ Pentium M 1.6 GHz processor■ 1 GB RAM■ 40 GB harddisk (5,400 rpm)■ Microsoft™ Windows XP™ Professional Multi-language OS installed■ Barco Server software for network communication between display server and clients■ DropZone software■ Proximity Desktop client software■ Remote Control & Diagnostics software
Energieverbruik	Max. 730 Watt
Wisselstroom	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
Veiligheidsvoorschriften	Compliant with ETL60950 and EN60950
Elektromagnetische storing	Compliant with FCC rules & regulations, part 15 CE EN55022 Class A and CCC
Afmetingen	Projector body with cable basket: W 415 mm (16.34") x H 195 mm (7.68") x D 565 mm (22.24") Without cable basket: D = 487 mm (19.17") Including lens: Dmax = 590 mm (23.23")
Gewicht	Net weight, body only: 16 kg (35.3 lbs) Shipping weight: max. 20 kg (44.1 lbs)

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.