

RLM-W14

14,500 lumens, WUXGA, 3-chip DLP projector



- **Active Stereo 3D**
- **Video over a single Cat 5 cable**
- **Extended warping and blending**

Featuring a stylish projector design with a very stable lens mount, the RLM-W14 offers Active Stereo 3D and provides video over a single Cat 5 cable (HDBaseTTM). It is designed for fixed installation in museums, theaters, houses of worship, hotels, lecture halls or conference auditoriums; but its extended warping and blending, rugged chassis and optional rental frame make it equally suited for the rental market as well.

Video over a single Cat 5 cable

Supporting point-to-point transmission of video signals – up to WUXGA (1,920 x 1,200) at 60 Hz – from a source converter to a projector over a single Cat 5 cable, the RLM-W14's HDBaseTTM technology takes away the need for multiple cables and connectors, leading to more simplicity and lower costs.

Stunning images

Geared with three-chip DLP technology, the high-brightness RLM-W14 generates crisp and stable images with rich contrast and sensational colors. It also features a DICOM simulated mode that guarantees accurate greyscales and highly detailed images – key requirements for medical training.

Rugged design

Operating on a voltage of 110V -240V, the RLM-W14 is a rugged projector that reduces noise and power consumption. Moreover, its TLD lenses are compatible with the RLM-W12, HDX and HDF projectors. It's also standard equipped with BarcoLink, allowing native WUXGA @60 Hz signals to be transmitted between the Barco image processors and projectors via a single BNC cable, for simple and reliable signal distribution.

- 14,500 lumens light output
- 3-chip DLP technology
- WUXGA (1,920 x 1,200) resolution
- Video over a single Cat 5 cable thanks to standard HDBaseTTM
- Standard Active Stereo 3D
- Extended warping and blending
- Better color stability & saturation
- Perfect for fixed installations
- Rental frame available
- Low power consumption
- Wide range of TLD lenses, compatible with RLM-W12, HDX, HDF and FLM projectors

Product specificaties**RLM-W14****General specifications**

Type projector	WUXGA 3-chip DLP digital projector
Technologie	0.96" DMD™ x3
Resolutie	1,920 x 1,200
Helderheid	14,500 center / 13,500 ANSI lumens*
Contrastverhouding	1,650:1 (standard) / 2,400:1 (CE)
Helderheidsuniformiteit	90%
Beeldverhouding	16:10
ScenergiX	Horizontal and vertical edge blending
Type lens	TLD+
Lenzen	0.73:1 ; 1.2:1 ; 1.16-1.5:1 ; 1.5-2.0:1 ; 2.0-2.8:1 ; 2.8-4.5:1 ; 4.5-7.5:1 ; 7.5-11.5:1
Optische lensverschuiving	Vertical: -70% to +130% / Horizontal: +/-30% on zoom lenses memorized
Kleurcorrectie	P7
Lampen	2x465W
Levensduur lamp	2,000 hours (typical) / 2,500 hours (maximum)
Lampgarantie	120 days, 500 hours
Verzegelde DLP™-kern	Standard
Optische dowser	Standard
Picture-in-Picture	Up to two sources simultaneously
Oriëntatie	table -ceiling
WARP	preset values + custom (RS232)
Geïntegreerde webserver	Yes
3D	Dual link DVI with sync in /out BNC
Ingangen	HDMI (HDCP 1.3); HDBase-T; 5-BNC (RGBHV, RGBS/RGBsB;YUV); VGA (RGBHV, RGBS/RGBsB;YUV); cinch (RGBs, YUV); HSDI/ 3G HDSDI /SDI; 3D DUAL LINK DVI
Invoerresoluties	From NTSC up to UXGA (1,600 x 1,200), including HDTV (1,920 x 1,200)
Max. pixelklok	165Mhz up to 200Mhz
Softwaretools	Projection Toolset + Android app + iOS app
Controle	Mini-jack + IR, RS232, 12v trigger
Netwerkverbinding	10/100 base-T, RJ-45 connection
Voedingsvereisten	90-240V / 50-60Hz -1,140W @ 240V, 1,230W @ 110V, STBY less than 2W
Geluidsniveau (standaard bij 25°C/77°F)	46 dB(A) norm, 42dB(A) eco
Operationele omgevingstemperatuur	0-40°C / 32°-104°F
Operationele vochtigheid	0-85% (non condens)
Dissipatie BTU	max 4,131 BTU/h
Afmetingen (B x L x H)	631 x 504 x 270 mm / 24.8 x 19.82 x 10.63 inches
Gewicht	33.5kg (73.8 lbs)
Verzendingsafmetingen	(LxWxH) 829 x 709 x 437 mm / 32.64 x 27.9 x 17.20 inches
Verzendgewicht af fabriek	41.5 kg (91.49 lbs)
Standaardaccessoires	Power cord, wireless remote control, HDMI to DVI adaptor
Certificeringen	Complies with FCC rules & regulations, part 15 Class A and CE EN55022 Class A, CE, TUV, RHoS, WEE
Garantie	3 years standard, extra 2 years optional
*	+/-10%

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

www.barco.com**BARCO**