

BarcoGraphics 9300



- Video Sources: VHS, S-VHS, Component (Y, R-Y, B-Y) and RGB format
- DVD, satellite receiver, laserdisc
- Computers and workstations with a resolution of up to 1,280 x 1,024 pixels
- Optional SDI (Serial digital input)
- High light output of 8,000 lumens full white
- Three active matrix 5.8" high aperture LCD panels with a resolution of 1,024 x 768
- Powerful 1800 Watt metal-halide lamp
- The advanced TCR + feature processes conventional video sources to a qualitative output result with vibrant colours and amazing colour depth
- The Patented Pixel Map Processor guarantees very legible characters and great picture detail

技术规格

BARCOGRAPHICS 9300

一般规格

兼容性

Video sources : VHS, S-VHS, Component and RGB format
DVD, Satellite receiver, laserdisc
Computers and workstations with a resolution of up to 1280 x 1024 pixels
Optional SDI (Serial Digital Input)

对比度

>160:1 (on 5x4 B/W checkerboard)
>300:1 (full white/full black)

光输出

8000 Lumen full white
7000 ANSI Lumen

屏幕尺寸

Min.: 1 m x .075 m (3.3' x 2.5')
Max.: 15 m x 11.25 m (50' x 37.5')

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。