

# ClickShare CX-50 2nd generation

Premium conferencing solution for high-impact rooms



- **Dual screen: people and content side by side on two displays**
- **Effortless switching between UC mode and BYOM experience**
- **Wired roomdock for 4K content sharing and alternative connectivity**
- **Carbon-neutral**
- **100% secure, encrypted and cloud-managed**

ClickShare CX-50 2nd generation brings flexible wireless conferencing in high-impact meeting spaces and board rooms. When you walk into the meeting room, ClickShare automatically connects you to room devices like cameras, mics, speakers, sound bars and displays.

Start a meeting from your laptop within seconds, using your preferred video conferencing platform. Make hybrid meetings easy, with just one click on the ClickShare Button or the ClickShare App, both for employees and guests.

**Product specifications****CLICKSHARE CX-50 2ND GENERATION**

| <b>ClickShare Base Unit dimensions</b>                               |  |
|--|--|
| Dimensions (HxWxD)   | 39mm x 200mm x 202mm   |
| Power supply   | Standard 110/220 V AC plug or USB-C (back)   |
| Power consumption  | Operational: 74.5W (max)<br>Standby: 0.27W -Networked standby: 3.7W  |
| Weight   | 985 gr   |
| <b>General specifications</b>  |  |
| Operating system   | Windows 10 or higher macOS 11 (BigSur) and higher<br>Android v11 and higher (ClickShare App)<br>iOS 14 and higher (ClickShare App)   |
| System requirements  | For a smooth experience with Microsoft Teams or Zoom<br>Minimum: Intel i3 dual-core processor / 8GB RAM / OS : Windows 10 latest build or Mojave latest build<br>Recommended: Intel i5 4-core processor / 8GB RAM / OS: Windows 10 latest build or Mac OS latest build |
| Video outputs  | 4K UHD (3840*2160) @ 60Hz. HDMI 1.4b<br><br>4K UHD (3840*2160) @ 60Hz.USB-C DP ALT mode (back)   |
| Video inputs   | 4k UHD (3840*2160) @30Hz.USB-C DP ALT mode (front)   |
| Audio output   | USB, jack, HDMI  |
| Connections  | Front side: 1x USB-C 3.1<br>Rear side: 1x USB-C 3.1, 2x USB -A 3.1, 1x Ethernet LAN 2.5Gbit, Audio analog line out on jack socket (3.5mm)  |
| ClickShare Buttons   | 2  |
| ClickShare App   | Desktop & Mobile   |
| Native protocols   | Airplay, Google Cast, Miracast   |
| Maximum number of simultaneous connections (with Buttons and/or App) | 32   |
| Noise Level  | Max. 25dBA @ 0-30°C<br>Max. 30dBA @ 30-40°C  |
| Authentication protocol  | WPA2-PSK in stand alone mode<br>WPA2-PSK or IEEE 802.1X using the ClickShare Button in network integration mode  |
| Wireless transmission protocol                                       | IEEE 802.11 a/g/n/ac and IEEE 802.15.1   |
| Reach  | Max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit   |
| Frequency band   | 2.4 GHZ and 5 GHz (DFS channels supported in select number of countries)   |
| Temperature range  | Operating: 0°C to +40°C (+32°F to +104°F)<br>Max: 35°C (95°F) at 3000m<br>Storage: -20°C to +60°C (-4°F to +140°F)   |
| Humidity   | Storage: 0 to 90% relative humidity, non-condensing<br>Operation: 0 to 85% relative humidity, non-condensing   |
| Anti-theft system  | Kensington lock  |
| Certifications   | FCC/CE   |
| Touch screen support & Interactivity                                 | Yes  |
| Wireless conferencing  | via App or Button  |
| Local view   | High quality   |
| Network connection   | LAN & WiFi (dual)  |
| Management and reporting   | Yes  |
| Warranty   | 1 year standard. 5 years coverage upon registering via SmartCare   |

Last updated: 12 Apr 2024

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.