

FLDX 2.5 - 4.6 (EN64) lens

Long Zoom lens with encoders



The EN64 is an all-glass lens that is designed to optimize the image quality and performance of your projection product. The internal lens elements are carefully selected and coated to achieve the highest resolution performance and the coatings are furthermore optimized for night vision and IR transmission for training with Night Vision Goggles. The lens comes with encoders for accurate positioning of zoom, focus and iris.

Can also be used on the Barco Fx400-HR series with adapter.

Can also be used on the Barco F80-series with adapter and related software.

Product specifications**FLDX 2.5 - 4.6 (EN64) LENS**

General specifications	
Working F/#	F 2.04-2.87 Motorized Iris F/2.04-6.0
Zoom ratio	1,85 Motorized zoom and focus
Platforms	For Fx40, Fx70, F80 (require a lens adaptor -R98014421), F90 and Fx400 (requires a lens adaptor -R9802623)
Throw Ratio	DMD chip 4K 2.19-4.05:1 WQXGA 2.50-4.63:1 WUXGA 2.33-4.32:1 TR: Front of lens, 111.4" @6m Image size tolerance +/-2%
Focal length	49.52-91.6 mm
Focus Range	Standard: 2.5m-25m (Optical)
Weight	3.08 kg

Last updated: 04 Jul 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.