

BARCOData 3200



Product specifications**BARCODATA 3200****General specifications**

Contrast	5x4 Checkerboard: 150:1 Full Field Contrast: 300:1
Depth	662 mm / 26 inch
Height	372 mm / 15 inch
Inputs	Communication: 1 D9-female Stereo Audio: 2 x Cinch (RCA) RGB trilevel sync, sync on green or sync separate: 5 x BNC (Optional) RGB analog standard sync, sync on green or sync separate: 5 x BNC (Optional) Component Video: 4 x BNC (Optional) Video/S-Video: 1 x BNC/4-pin DIN (Optional) RS232 loop-through: 1 x D9-female
Light output	ANSI Normal: 1200 Lumen Full White: 1450 Lumen Equivalent CRT Peak White: 5000 Lumen
Outputs	RS232 loop-through: 1 x D9-male Stereo Audio: 2 x Cinch (RCA)
Resolution	True LCD Panel Resolution 720 x 480 Maximum Display Resolution 800 x 600
Screen size	Minimum Screen Width 1m Maximum Screen Width 10m
Weight	Net weight 45 kg / 99 lbs Shipping weight 57 kg / 126 lbs
Width	633 mm / 25 inch

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.